

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582968

Luminaire Tested: **HCC6W05D010MW-HM60525935-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582968  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W05D010MW-HM60525935-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 677.7 lumens  
Efficiency: N/A  
Efficacy: 112.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582968  
CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P582968  
 CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	25272
5°	25490
10°	26408
15°	28683
20°	29834
25°	28538
30°	24630
35°	17735
40°	9990
45°	5179
50°	3087
55°	2227
60°	1897
65°	2179
70°	2773
75°	2923
80°	2841
85°	2705



TEST NUMBER: P582968  
 CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	6.6
10°-20°	142.6	21.0
20°-30°	213.1	31.4
30°-40°	162.9	24.0
40°-50°	56.9	8.4
50°-60°	21.7	3.2
60°-70°	17.0	2.5
70°-80°	14.4	2.1
80°-90°	4.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.2	59.1
0°-40°	563.1	83.1
0°-60°	641.7	94.7
0°-90°	677.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	461	
5°	463	45
15°	505	143
25°	472	213
35°	265	163
45°	67	57
55°	23	22
65°	17	17
75°	14	14
85°	4	5
90°	0	



TEST NUMBER: P582968  
CATALOG NUMBER: HCC6W05D010MW-HM60525935-61WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	461.0
2.5°	459.8
5°	463.2
7.5°	467.9
10°	474.4
12.5°	489.1
15°	505.4
17.5°	515.4
20°	511.4
22.5°	496.0
25°	471.8
27.5°	437.3
30°	389.1
32.5°	331.3
35°	265.0
37.5°	196.5
40°	139.6
42.5°	97.9
45°	66.8
47.5°	47.0
50°	36.2
52.5°	28.5
55°	23.3
57.5°	19.0
60°	17.3
62.5°	16.8
65°	16.8
67.5°	17.6
70°	17.3
72.5°	15.9
75°	13.8
77.5°	11.6
80°	9.0
82.5°	6.4
85°	4.3
87.5°	1.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)