

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582977

Luminaire Tested: **HCC6S05D010BZ-HM60525940-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010BZ-HM60525940-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 633.4 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582977
CATALOG NUMBER: HCC6S05D010BZ-HM60525940-61NDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582977

CATALOG NUMBER: HCC6S05D010BZ-HM60525940-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93	
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75	
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61	
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57	
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54	
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38774
5°	38609
10°	37697
15°	35778
20°	31894
25°	26868
30°	21402
35°	15265
40°	8208
45°	3520
50°	1603
55°	583
60°	285
65°	221
70°	224
75°	106
80°	158
85°	0



TEST NUMBER: P582977
 CATALOG NUMBER: HCC6S05D010BZ-HM60525940-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.2	10.5
10°-20°	174.8	27.6
20°-30°	202.4	32.0
30°-40°	139.9	22.1
40°-50°	40.4	6.4
50°-60°	6.9	1.1
60°-70°	1.8	0.3
70°-80°	0.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	443.4	70.0
0°-40°	583.3	92.1
0°-60°	630.7	99.6
0°-90°	633.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	633.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	707	
5°	702	66
15°	630	175
25°	444	202
35°	228	140
45°	45	40
55°	6	7
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P582977
CATALOG NUMBER: HCC6S05D010BZ-HM60525940-61NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	707.3
2.5°	704.2
5°	701.6
7.5°	693.7
10°	677.2
12.5°	657.1
15°	630.4
17.5°	592.9
20°	546.7
22.5°	495.6
25°	444.2
27.5°	391.3
30°	338.1
32.5°	284.9
35°	228.1
37.5°	169.3
40°	114.7
42.5°	72.4
45°	45.4
47.5°	29.3
50°	18.8
52.5°	11.3
55°	6.1
57.5°	3.5
60°	2.6
62.5°	2.1
65°	1.7
67.5°	1.4
70°	1.4
72.5°	0.9
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)