

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593008

Luminaire Tested: **HCC6S05D010BZ-HM60525950-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010BZ-HM60525950-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 593.7 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593008
CATALOG NUMBER: HCC6S05D010BZ-HM60525950-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P593008

CATALOG NUMBER: HCC6S05D010BZ-HM60525950-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22487
5°	22381
10°	21882
15°	21374
20°	20570
25°	19453
30°	17674
35°	14308
40°	9647
45°	6629
50°	5433
55°	4750
60°	4495
65°	4255
70°	3991
75°	3791
80°	3473
85°	2956



TEST NUMBER: P593008
 CATALOG NUMBER: HCC6S05D010BZ-HM60525950-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	6.5
10°-20°	105.8	17.8
20°-30°	146.9	24.7
30°-40°	130.8	22.0
40°-50°	69.5	11.7
50°-60°	45.4	7.6
60°-70°	32.6	5.5
70°-80°	18.9	3.2
80°-90°	5.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.1	49.0
0°-40°	421.9	71.1
0°-60°	536.7	90.4
0°-90°	593.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	410	
5°	407	38
15°	377	106
25°	322	147
35°	214	131
45°	86	69
55°	50	45
65°	33	33
75°	18	19
85°	5	5
90°	0	



TEST NUMBER: P593008
CATALOG NUMBER: HCC6S05D010BZ-HM60525950-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	410.2
2.5°	408.0
5°	406.7
7.5°	401.9
10°	393.1
12.5°	385.3
15°	376.6
17.5°	365.7
20°	352.6
22.5°	337.8
25°	321.6
27.5°	302.8
30°	279.2
32.5°	250.9
35°	213.8
37.5°	172.8
40°	134.8
42.5°	104.8
45°	85.5
47.5°	72.9
50°	63.7
52.5°	56.3
55°	49.7
57.5°	45.0
60°	41.0
62.5°	37.1
65°	32.8
67.5°	28.8
70°	24.9
72.5°	21.4
75°	17.9
77.5°	14.4
80°	11.0
82.5°	7.9
85°	4.7
87.5°	2.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)