

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583285

Luminaire Tested: **HCC6S07D010MW-HM60525827-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MW-HM60525827-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 832.1 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583285
CATALOG NUMBER: HCC6S07D010MW-HM60525827-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583285

CATALOG NUMBER: HCC6S07D010MW-HM60525827-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29740
5°	29655
10°	29213
15°	28752
20°	27810
25°	26481
30°	24181
35°	19475
40°	13117
45°	9567
50°	8273
55°	7474
60°	7094
65°	6706
70°	6315
75°	5973
80°	5588
85°	5221



TEST NUMBER: P583285
 CATALOG NUMBER: HCC6S07D010MW-HM60525827-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	6.1
10°-20°	142.3	17.1
20°-30°	199.9	24.0
30°-40°	177.9	21.4
40°-50°	99.4	11.9
50°-60°	70.9	8.5
60°-70°	51.6	6.2
70°-80°	29.8	3.6
80°-90°	9.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.1	47.2
0°-40°	571.1	68.6
0°-60°	741.4	89.1
0°-90°	832.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	832.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	542	
5°	539	51
15°	507	142
25°	438	200
35°	291	178
45°	123	99
55°	78	71
65°	52	52
75°	28	30
85°	8	9
90°	0	



TEST NUMBER: P583285
CATALOG NUMBER: HCC6S07D010MW-HM60525827-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	542.5
2.5°	540.1
5°	538.9
7.5°	534.2
10°	524.8
12.5°	516.0
15°	506.6
17.5°	493.6
20°	476.7
22.5°	457.8
25°	437.8
27.5°	413.1
30°	382.0
32.5°	342.1
35°	291.0
37.5°	233.3
40°	183.3
42.5°	146.4
45°	123.4
47.5°	108.1
50°	97.0
52.5°	87.0
55°	78.2
57.5°	71.2
60°	64.7
62.5°	58.8
65°	51.7
67.5°	45.9
70°	39.4
72.5°	33.5
75°	28.2
77.5°	22.9
80°	17.7
82.5°	12.9
85°	8.3
87.5°	4.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)