

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583309

Luminaire Tested: **HCC6W07D010BZ-HM60525830-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010BZ-HM60525830-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 922.7 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583309
CATALOG NUMBER: HCC6W07D010BZ-HM60525830-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P583309

CATALOG NUMBER: HCC6W07D010BZ-HM60525830-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31483
5°	31466
10°	31162
15°	30840
20°	29968
25°	28701
30°	26637
35°	22914
40°	16724
45°	11466
50°	9219
55°	8038
60°	7412
65°	7057
70°	6572
75°	6164
80°	5588
85°	4780



TEST NUMBER: P583309
 CATALOG NUMBER: HCC6W07D010BZ-HM60525830-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	5.9
10°-20°	152.6	16.5
20°-30°	217.0	23.5
30°-40°	208.9	22.6
40°-50°	120.2	13.0
50°-60°	76.2	8.3
60°-70°	53.9	5.8
70°-80°	30.7	3.3
80°-90°	8.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	45.9
0°-40°	632.8	68.6
0°-60°	829.2	89.9
0°-90°	922.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	922.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	572	54
15°	543	153
25°	474	217
35°	342	209
45°	148	120
55°	84	76
65°	54	54
75°	29	31
85°	8	9
90°	0	



TEST NUMBER: P583309

CATALOG NUMBER: HCC6W07D010BZ-HM60525830-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.3
2.5°	571.8
5°	571.8
7.5°	568.0
10°	559.8
12.5°	551.5
15°	543.4
17.5°	530.7
20°	513.7
22.5°	494.7
25°	474.5
27.5°	449.8
30°	420.8
32.5°	385.4
35°	342.4
37.5°	290.0
40°	233.7
42.5°	184.5
45°	147.9
47.5°	124.5
50°	108.1
52.5°	94.7
55°	84.1
57.5°	74.6
60°	67.6
62.5°	61.3
65°	54.4
67.5°	48.0
70°	41.0
72.5°	34.8
75°	29.1
77.5°	23.3
80°	17.7
82.5°	12.7
85°	7.6
87.5°	3.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)