

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583339

Luminaire Tested: **HCC6W07D010MW-HM60525840-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010MW-HM60525840-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 938.4 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583339
CATALOG NUMBER: HCC6W07D010MW-HM60525840-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583339

CATALOG NUMBER: HCC6W07D010MW-HM60525840-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78		
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56		
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51		
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43		
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39		
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33539
5°	33452
10°	32954
15°	32429
20°	31363
25°	29875
30°	27276
35°	21957
40°	14799
45°	10792
50°	9322
55°	8420
60°	8004
65°	7562
70°	7117
75°	6736
80°	6282
85°	5850



TEST NUMBER: P583339

CATALOG NUMBER: HCC6W07D010MW-HM60525840-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	6.1
10°-20°	160.5	17.1
20°-30°	225.5	24.0
30°-40°	200.7	21.4
40°-50°	112.2	12.0
50°-60°	79.9	8.5
60°-70°	58.1	6.2
70°-80°	33.6	3.6
80°-90°	10.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	443.5	47.3
0°-40°	644.1	68.6
0°-60°	836.2	89.1
0°-90°	938.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	938.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	612	
5°	608	58
15°	571	160
25°	494	225
35°	328	201
45°	139	112
55°	88	80
65°	58	58
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P583339

CATALOG NUMBER: HCC6W07D010MW-HM60525840-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	611.8
2.5°	609.2
5°	607.9
7.5°	602.5
10°	592.0
12.5°	582.0
15°	571.4
17.5°	556.9
20°	537.6
22.5°	516.4
25°	493.9
27.5°	466.0
30°	430.9
32.5°	385.8
35°	328.1
37.5°	263.2
40°	206.8
42.5°	165.1
45°	139.2
47.5°	122.0
50°	109.3
52.5°	98.1
55°	88.1
57.5°	80.2
60°	73.0
62.5°	66.3
65°	58.3
67.5°	51.7
70°	44.4
72.5°	37.7
75°	31.8
77.5°	25.8
80°	19.9
82.5°	14.6
85°	9.3
87.5°	4.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)