

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583375

Luminaire Tested: **HCC6S07D010SL-HM60525930-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525930-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 767.1 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583375
CATALOG NUMBER: HCC6S07D010SL-HM60525930-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583375
 CATALOG NUMBER: HCC6S07D010SL-HM60525930-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78		
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56		
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51		
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43		
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39		
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27416
5°	27339
10°	26931
15°	26504
20°	25634
25°	24419
30°	22288
35°	17949
40°	12094
45°	8823
50°	7624
55°	6891
60°	6535
65°	6187
70°	5818
75°	5528
80°	5114
85°	4780



TEST NUMBER: P583375
 CATALOG NUMBER: HCC6S07D010SL-HM60525930-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	6.1
10°-20°	131.1	17.1
20°-30°	184.3	24.0
30°-40°	164.0	21.4
40°-50°	91.7	12.0
50°-60°	65.3	8.5
60°-70°	47.5	6.2
70°-80°	27.5	3.6
80°-90°	8.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.4	47.2
0°-40°	526.5	68.6
0°-60°	683.5	89.1
0°-90°	767.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	767.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	500	
5°	497	47
15°	467	131
25°	404	184
35°	268	164
45°	114	92
55°	72	65
65°	48	48
75°	26	28
85°	8	9
90°	0	



TEST NUMBER: P583375

CATALOG NUMBER: HCC6S07D010SL-HM60525930-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	500.1
2.5°	498.0
5°	496.8
7.5°	492.5
10°	483.8
12.5°	475.7
15°	467.0
17.5°	455.1
20°	439.4
22.5°	422.0
25°	403.7
27.5°	380.9
30°	352.1
32.5°	315.3
35°	268.2
37.5°	215.2
40°	169.0
42.5°	134.9
45°	113.8
47.5°	99.7
50°	89.4
52.5°	80.2
55°	72.1
57.5°	65.6
60°	59.6
62.5°	54.2
65°	47.7
67.5°	42.3
70°	36.3
72.5°	30.9
75°	26.1
77.5°	21.2
80°	16.2
82.5°	11.9
85°	7.6
87.5°	3.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)