

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583381

Luminaire Tested: **HCC6W07D010BZ-HM60525930-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583381
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010BZ-HM60525930-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 790.9 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583381
CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P583381

CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56								
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51								
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39								
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26988
5°	26970
10°	26708
15°	26436
20°	25686
25°	24600
30°	22833
35°	19649
40°	14341
45°	9830
50°	7897
55°	6891
60°	6348
65°	6045
70°	5642
75°	5274
80°	4799
85°	4088



TEST NUMBER: P583381
 CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	5.9
10°-20°	130.8	16.5
20°-30°	186.0	23.5
30°-40°	179.1	22.6
40°-50°	103.1	13.0
50°-60°	65.3	8.3
60°-70°	46.2	5.8
70°-80°	26.4	3.3
80°-90°	7.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.3	45.9
0°-40°	542.4	68.6
0°-60°	710.8	89.9
0°-90°	790.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	492	
5°	490	46
15°	466	131
25°	407	186
35°	294	179
45°	127	103
55°	72	65
65°	47	46
75°	25	26
85°	6	8
90°	0	



TEST NUMBER: P583381
CATALOG NUMBER: HCC6W07D010BZ-HM60525930-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	492.3
2.5°	490.1
5°	490.1
7.5°	486.9
10°	479.8
12.5°	472.8
15°	465.8
17.5°	454.9
20°	440.3
22.5°	424.1
25°	406.7
27.5°	385.6
30°	360.7
32.5°	330.4
35°	293.6
37.5°	248.6
40°	200.4
42.5°	158.2
45°	126.8
47.5°	106.7
50°	92.6
52.5°	81.2
55°	72.1
57.5°	63.9
60°	57.9
62.5°	52.6
65°	46.6
67.5°	41.1
70°	35.2
72.5°	29.8
75°	24.9
77.5°	20.1
80°	15.2
82.5°	10.9
85°	6.5
87.5°	2.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)