

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583388

Luminaire Tested: **HCC6S07D010MW-HM60525935-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MW-HM60525935-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 808.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583388
CATALOG NUMBER: HCC6S07D010MW-HM60525935-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P583388

CATALOG NUMBER: HCC6S07D010MW-HM60525935-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40474
5°	40441
10°	40018
15°	39211
20°	37138
25°	33540
30°	28492
35°	21034
40°	12173
45°	6458
50°	3650
55°	1902
60°	1250
65°	882
70°	641
75°	487
80°	347
85°	377



TEST NUMBER: P583388
 CATALOG NUMBER: HCC6S07D010MW-HM60525935-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.6	8.6
10°-20°	193.2	23.9
20°-30°	252.2	31.2
30°-40°	192.7	23.9
40°-50°	69.8	8.6
50°-60°	20.3	2.5
60°-70°	7.2	0.9
70°-80°	2.5	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.1	63.7
0°-40°	707.8	87.6
0°-60°	797.9	98.7
0°-90°	808.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	738	
5°	735	70
15°	691	193
25°	554	252
35°	314	193
45°	83	70
55°	20	20
65°	7	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P583388
CATALOG NUMBER: HCC6S07D010MW-HM60525935-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	738.3
2.5°	734.9
5°	734.9
7.5°	729.7
10°	718.9
12.5°	706.3
15°	690.9
17.5°	668.0
20°	636.6
22.5°	597.9
25°	554.5
27.5°	505.4
30°	450.1
32.5°	387.9
35°	314.3
37.5°	237.4
40°	170.1
42.5°	117.5
45°	83.3
47.5°	59.9
50°	42.8
52.5°	30.3
55°	19.9
57.5°	14.3
60°	11.4
62.5°	9.2
65°	6.8
67.5°	5.7
70°	4.0
72.5°	2.8
75°	2.3
77.5°	1.7
80°	1.1
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)