

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583392

Luminaire Tested: **HCC6W07D010SL-HM60525935-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583392  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W07D010SL-HM60525935-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 776.1 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583392  
CATALOG NUMBER: HCC6W07D010SL-HM60525935-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583392

CATALOG NUMBER: HCC6W07D010SL-HM60525935-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29395
5°	29259
10°	28607
15°	27940
20°	26888
25°	25435
30°	23111
35°	18705
40°	12616
45°	8668
50°	7104
55°	6212
60°	5877
65°	5552
70°	5209
75°	4935
80°	4514
85°	3900



TEST NUMBER: P583392  
 CATALOG NUMBER: HCC6W07D010SL-HM60525935-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	6.5
10°-20°	138.2	17.8
20°-30°	192.1	24.7
30°-40°	171.0	22.0
40°-50°	90.8	11.7
50°-60°	59.4	7.7
60°-70°	42.5	5.5
70°-80°	24.7	3.2
80°-90°	7.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.5	49.0
0°-40°	551.5	71.1
0°-60°	701.7	90.4
0°-90°	776.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	776.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	536	
5°	532	50
15°	492	138
25°	420	192
35°	280	171
45°	112	91
55°	65	59
65°	43	43
75°	23	25
85°	6	7
90°	0	



TEST NUMBER: P583392  
CATALOG NUMBER: HCC6W07D010SL-HM60525935-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	536.2
2.5°	533.4
5°	531.7
7.5°	525.4
10°	513.9
12.5°	503.7
15°	492.3
17.5°	478.0
20°	460.9
22.5°	441.5
25°	420.5
27.5°	395.9
30°	365.1
32.5°	328.0
35°	279.5
37.5°	225.9
40°	176.3
42.5°	136.9
45°	111.8
47.5°	95.3
50°	83.3
52.5°	73.6
55°	65.0
57.5°	58.8
60°	53.6
62.5°	48.5
65°	42.8
67.5°	37.6
70°	32.5
72.5°	28.0
75°	23.3
77.5°	18.8
80°	14.3
82.5°	10.3
85°	6.2
87.5°	2.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)