

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583408

Luminaire Tested: **HCC6S07D010BZ-HM60525940-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010BZ-HM60525940-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 879.3 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583408
CATALOG NUMBER: HCC6S07D010BZ-HM60525940-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583408

CATALOG NUMBER: HCC6S07D010BZ-HM60525940-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94	94	94	94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76	76	76	76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71	71	71	71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67	67	67	67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52518
5°	52625
10°	53489
15°	53877
20°	49249
25°	38700
30°	28327
35°	20090
40°	9504
45°	3628
50°	1620
55°	440
60°	186
65°	143
70°	96
75°	127
80°	0
85°	0



TEST NUMBER: P583408
 CATALOG NUMBER: HCC6S07D010BZ-HM60525940-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	10.4
10°-20°	262.4	29.8
20°-30°	291.8	33.2
30°-40°	182.3	20.7
40°-50°	43.3	4.9
50°-60°	6.2	0.7
60°-70°	1.2	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.7	73.4
0°-40°	828.0	94.2
0°-60°	877.5	99.8
0°-90°	879.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	879.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	958	
5°	956	91
15°	949	262
25°	640	292
35°	300	182
45°	47	43
55°	5	6
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583408
CATALOG NUMBER: HCC6S07D010BZ-HM60525940-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	958.0
2.5°	954.0
5°	956.3
7.5°	959.8
10°	960.9
12.5°	960.3
15°	949.3
17.5°	912.4
20°	844.2
22.5°	748.3
25°	639.8
27.5°	535.9
30°	447.5
32.5°	374.2
35°	300.2
37.5°	220.6
40°	132.8
42.5°	76.8
45°	46.8
47.5°	30.0
50°	19.0
52.5°	11.0
55°	4.6
57.5°	2.3
60°	1.7
62.5°	1.7
65°	1.1
67.5°	1.1
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)