

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583701

Luminaire Tested: **HCC8S10D010BZ-HM80520827-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010BZ-HM80520827-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1158.1 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583701
CATALOG NUMBER: HCC8S10D010BZ-HM80520827-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583701
 CATALOG NUMBER: HCC8S10D010BZ-HM80520827-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27182
5°	26831
10°	25845
15°	24834
20°	24149
25°	23422
30°	21019
35°	13778
40°	7616
45°	6349
50°	5790
55°	5527
60°	5137
65°	4655
70°	4219
75°	3813
80°	3463
85°	3326



TEST NUMBER: P583701
 CATALOG NUMBER: HCC8S10D010BZ-HM80520827-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	7.0
10°-20°	219.5	19.0
20°-30°	312.4	27.0
30°-40°	231.2	20.0
40°-50°	114.5	9.9
50°-60°	91.4	7.9
60°-70°	63.4	5.5
70°-80°	34.2	3.0
80°-90°	10.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.3	53.0
0°-40°	844.5	72.9
0°-60°	1050.3	90.7
0°-90°	1158.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1158.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	882	
5°	867	81
15°	778	219
25°	688	312
35°	366	231
45°	146	114
55°	103	91
65°	64	63
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P583701
CATALOG NUMBER: HCC8S10D010BZ-HM80520827-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	881.5
2.5°	877.6
5°	866.8
7.5°	849.6
10°	825.4
12.5°	800.5
15°	777.9
17.5°	756.2
20°	735.9
22.5°	715.7
25°	688.4
27.5°	648.7
30°	590.3
32.5°	500.8
35°	366.0
37.5°	250.0
40°	189.2
42.5°	162.0
45°	145.6
47.5°	132.3
50°	120.7
52.5°	110.6
55°	102.8
57.5°	93.4
60°	83.3
62.5°	73.2
65°	63.8
67.5°	54.5
70°	46.8
72.5°	38.9
75°	32.0
77.5°	25.7
80°	19.5
82.5°	14.1
85°	9.4
87.5°	3.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)