

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583697

Luminaire Tested: **HCC8S10D010SL-HM80520827-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583697
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010SL-HM80520827-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1153.3 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583697
CATALOG NUMBER: HCC8S10D010SL-HM80520827-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583697

CATALOG NUMBER: HCC8S10D010SL-HM80520827-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29492
5°	28685
10°	26997
15°	25562
20°	24585
25°	23633
30°	20994
35°	13371
40°	7459
45°	6249
50°	5642
55°	5317
60°	4847
65°	4378
70°	3859
75°	3431
80°	3054
85°	2760



TEST NUMBER: P583697
 CATALOG NUMBER: HCC8S10D010SL-HM80520827-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.4	7.5
10°-20°	225.8	19.6
20°-30°	315.0	27.3
30°-40°	226.7	19.7
40°-50°	112.3	9.7
50°-60°	87.9	7.6
60°-70°	59.5	5.2
70°-80°	30.9	2.7
80°-90°	8.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.2	54.4
0°-40°	853.8	74.0
0°-60°	1054.0	91.4
0°-90°	1153.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1153.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	956	
5°	927	86
15°	801	226
25°	695	315
35°	355	227
45°	143	112
55°	99	88
65°	60	59
75°	29	31
85°	8	9
90°	0	



TEST NUMBER: P583697
CATALOG NUMBER: HCC8S10D010SL-HM80520827-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	956.4
2.5°	947.8
5°	926.7
7.5°	897.2
10°	862.2
12.5°	829.4
15°	800.7
17.5°	773.4
20°	749.2
22.5°	725.0
25°	694.6
27.5°	651.1
30°	589.6
32.5°	492.9
35°	355.2
37.5°	242.2
40°	185.3
42.5°	159.6
45°	143.3
47.5°	129.3
50°	117.6
52.5°	107.5
55°	98.9
57.5°	88.8
60°	78.6
62.5°	68.5
65°	60.0
67.5°	51.4
70°	42.8
72.5°	35.8
75°	28.8
77.5°	22.6
80°	17.2
82.5°	12.5
85°	7.8
87.5°	3.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)