

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583700

Luminaire Tested: **HCC8W10D010MW-HM80520827-81NDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583700  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MW-HM80520827-81NDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1042.8 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583700  
CATALOG NUMBER: HCC8W10D010MW-HM80520827-81NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583700  
 CATALOG NUMBER: HCC8W10D010MW-HM80520827-81NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	25989
5°	25921
10°	25491
15°	25118
20°	24513
25°	23269
30°	19196
35°	9882
40°	6614
45°	5674
50°	4893
55°	4274
60°	3793
65°	3415
70°	3092
75°	2776
80°	2504
85°	2477



TEST NUMBER: P583700  
 CATALOG NUMBER: HCC8W10D010MW-HM80520827-81NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.2	7.6
10°-20°	221.4	21.2
20°-30°	306.7	29.4
30°-40°	184.2	17.7
40°-50°	100.8	9.7
50°-60°	71.6	6.9
60°-70°	46.5	4.5
70°-80°	24.9	2.4
80°-90°	7.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.3	58.2
0°-40°	791.5	75.9
0°-60°	964.0	92.4
0°-90°	1042.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1042.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	843	
5°	837	79
15°	787	221
25°	684	307
35°	262	184
45°	130	101
55°	80	72
65°	47	47
75°	23	25
85°	7	7
90°	0	



TEST NUMBER: P583700  
CATALOG NUMBER: HCC8W10D010MW-HM80520827-81NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	842.8
2.5°	841.3
5°	837.4
7.5°	828.1
10°	814.1
12.5°	800.8
15°	786.8
17.5°	768.9
20°	747.0
22.5°	720.6
25°	683.9
27.5°	626.4
30°	539.1
32.5°	395.0
35°	262.5
37.5°	194.0
40°	164.3
42.5°	145.7
45°	130.1
47.5°	115.3
50°	102.0
52.5°	89.5
55°	79.5
57.5°	70.1
60°	61.5
62.5°	53.7
65°	46.8
67.5°	39.8
70°	34.3
72.5°	28.0
75°	23.3
77.5°	18.8
80°	14.1
82.5°	10.1
85°	7.0
87.5°	3.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)