

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583714

Luminaire Tested: **HCC8W10D010MB-HM80520830-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P583714
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8W10D010MB-HM80520830-81MDW
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
 Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
 CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1147.1 lumens
 Efficiency: N/A
 Efficacy: 115.9 lumens/watt
 Spacing Criteria (0/90/45): 1 / 1 / 0.95
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 9.9
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P583714
CATALOG NUMBER: HCC8W10D010MB-HM80520830-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583714

CATALOG NUMBER: HCC8W10D010MB-HM80520830-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29328
5°	28533
10°	26850
15°	25421
20°	24451
25°	23507
30°	20876
35°	13300
40°	7423
45°	6219
50°	5613
55°	5285
60°	4829
65°	4349
70°	3841
75°	3407
80°	3037
85°	2724



TEST NUMBER: P583714
 CATALOG NUMBER: HCC8W10D010MB-HM80520830-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	7.5
10°-20°	224.6	19.6
20°-30°	313.3	27.3
30°-40°	225.4	19.7
40°-50°	111.7	9.7
50°-60°	87.4	7.6
60°-70°	59.2	5.2
70°-80°	30.7	2.7
80°-90°	8.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	623.8	54.4
0°-40°	849.2	74.0
0°-60°	1048.4	91.4
0°-90°	1147.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1147.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	951	
5°	922	86
15°	796	225
25°	691	313
35°	353	225
45°	143	112
55°	98	87
65°	60	59
75°	29	31
85°	8	9
90°	0	



TEST NUMBER: P583714
CATALOG NUMBER: HCC8W10D010MB-HM80520830-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	951.1
2.5°	942.6
5°	921.8
7.5°	892.4
10°	857.5
12.5°	824.9
15°	796.3
17.5°	769.2
20°	745.1
22.5°	721.1
25°	690.9
27.5°	647.5
30°	586.3
32.5°	490.3
35°	353.3
37.5°	240.9
40°	184.4
42.5°	158.8
45°	142.6
47.5°	128.6
50°	117.0
52.5°	106.9
55°	98.3
57.5°	88.3
60°	78.3
62.5°	68.2
65°	59.6
67.5°	51.1
70°	42.6
72.5°	35.6
75°	28.6
77.5°	22.5
80°	17.1
82.5°	12.4
85°	7.7
87.5°	3.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)