

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583737

Luminaire Tested: **HCC8S10D010SL-HM80520835-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010SL-HM80520835-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1115.2 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583737
CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583737

CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	18345	18345	18345
5°	18690	18266	17842
10°	18981	17945	17190
15°	19170	17498	16444
20°	19099	16824	15686
25°	18594	15852	14807
30°	17711	14691	13947
35°	15991	13413	12953
40°	14053	12040	12004
45°	12128	10580	11037
50°	10559	9278	9902
55°	9354	8059	8618
60°	8357	6815	7160
65°	7523	5523	5647
70°	6690	4138	3336
75°	5755	2407	1442
80°	4439	852	426
85°	2866	283	283



TEST NUMBER: P583737
 CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.8	5.0
10°-20°	155.5	13.9
20°-30°	219.9	19.7
30°-40°	231.7	20.8
40°-50°	196.9	17.7
50°-60°	141.8	12.7
60°-70°	81.8	7.3
70°-80°	28.0	2.5
80°-90°	3.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.2	38.7
0°-40°	662.9	59.4
0°-60°	1001.6	89.8
0°-90°	1115.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1115.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	595	595	595	595	595	
5°	604	600	590	580	576	58
15°	600	582	548	524	515	169
25°	546	518	466	442	435	251
35°	425	400	356	343	344	265
45°	278	265	243	244	253	216
55°	174	160	150	156	160	157
65°	103	89	76	74	77	103
75°	48	36	20	13	12	51
85°	8	5	1	1	1	11
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583737

CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9
2.5°	600.5	601.4	600.5	600.5	599.7	599.0	598.1	597.3	595.7	594.0	594.0
5°	603.8	605.3	603.8	603.8	601.4	599.7	598.1	595.7	592.5	590.1	590.1
7.5°	606.2	606.2	606.2	603.8	602.1	599.7	595.7	591.6	587.7	583.6	582.0
10°	606.2	606.2	605.3	602.1	600.5	595.7	591.6	586.0	580.3	574.7	573.1
12.5°	603.8	604.5	602.9	599.7	595.7	590.1	584.4	577.1	570.7	564.2	561.0
15°	600.5	599.7	598.1	594.0	589.2	582.0	576.4	568.3	559.4	551.4	548.1
17.5°	592.5	592.5	590.1	586.0	579.6	571.6	562.7	553.8	544.1	535.3	531.2
20°	582.0	582.0	578.8	574.0	567.5	557.0	547.3	536.8	525.5	516.7	512.7
22.5°	566.6	567.5	563.4	557.8	550.5	538.5	528.8	515.9	504.6	494.1	490.9
25°	546.5	548.1	544.1	538.5	528.8	518.3	506.2	494.1	481.2	470.7	465.9
27.5°	523.1	524.0	519.9	514.2	504.6	493.3	481.2	468.3	456.3	445.0	440.1
30°	497.4	494.1	492.5	485.2	474.8	465.1	451.4	440.9	428.0	418.3	412.6
32.5°	461.1	462.6	457.8	452.2	444.1	432.8	421.5	409.5	397.4	390.2	386.1
35°	424.8	426.3	423.9	418.3	409.5	399.8	388.5	379.7	369.1	360.4	356.3
37.5°	386.9	386.9	385.2	382.1	375.6	366.7	355.4	346.7	337.8	330.4	328.0
40°	349.1	347.4	346.7	344.1	338.6	330.4	323.2	316.0	307.1	302.3	299.1
42.5°	311.9	311.9	310.4	308.0	302.3	298.2	291.0	283.0	276.5	271.7	271.7
45°	278.1	278.9	276.5	274.9	271.7	265.2	258.8	253.1	247.5	244.2	242.6
47.5°	248.2	248.2	245.8	244.2	241.0	235.4	229.7	224.9	220.8	218.4	217.7
50°	220.1	220.1	220.1	216.0	212.0	207.9	204.0	198.3	195.9	194.2	193.4
52.5°	195.9	195.1	195.1	191.8	187.8	182.9	179.0	174.0	171.6	170.1	170.9
55°	174.0	174.0	173.3	169.2	165.3	160.3	156.4	152.3	150.7	149.2	149.9
56°	165.3	165.3	164.4	161.2	156.4	152.3	147.5	143.5	141.1	141.8	141.8
57°	158.8	157.2	157.2	153.1	149.2	143.5	139.4	135.5	133.8	132.9	132.9
58°	150.7	149.9	149.2	145.1	141.1	136.2	132.2	128.1	125.7	125.7	124.9
59°	142.7	142.7	141.1	137.9	133.8	129.0	124.9	120.9	118.5	117.7	117.7
60°	135.5	136.2	133.8	130.5	127.4	121.8	116.8	113.7	111.2	110.5	110.5
61°	129.0	129.0	127.4	123.3	119.2	115.3	110.5	106.4	104.8	103.1	103.1
62°	123.3	121.8	120.9	116.8	112.9	108.1	104.0	100.0	97.5	95.9	96.8
63°	116.1	115.3	113.7	110.5	106.4	101.6	96.8	93.5	91.1	88.7	89.4
64°	110.5	109.6	107.2	104.0	100.0	95.1	90.3	87.0	85.5	83.1	82.2
65°	103.1	102.4	101.6	97.5	93.5	88.7	84.6	81.4	79.0	77.4	75.7
66°	96.8	97.5	95.9	92.7	87.9	83.8	78.1	75.0	73.3	70.9	69.4
67°	91.1	91.1	89.4	86.3	81.4	77.4	73.3	69.4	67.0	64.4	63.7
67.5°	87.9	87.9	86.3	82.2	79.0	74.2	70.1	67.0	63.7	62.0	60.5
68°	84.6	84.6	83.8	80.7	76.6	71.8	67.7	63.7	60.5	58.1	57.2
69°	79.0	79.8	78.1	75.0	70.9	66.1	62.0	58.9	55.7	53.2	51.6
70°	74.2	73.3	71.8	68.5	64.4	61.3	57.2	53.2	50.0	46.8	45.9
71°	67.7	67.7	66.1	63.7	59.6	55.7	51.6	48.3	45.2	41.1	40.3
72°	62.9	62.9	61.3	58.1	54.8	50.7	46.8	42.7	40.3	36.3	34.6
72.5°	59.6	60.5	58.9	55.7	52.4	47.6	44.4	41.1	37.0	33.9	32.2
73°	58.1	57.2	56.4	53.2	49.2	45.9	41.9	38.7	34.6	31.5	29.8



TEST NUMBER: P583737
 CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	36.3	36.3	35.5	32.2	29.0	25.8	22.6	19.4	16.1	12.9	11.3
80°	25.0	25.8	24.2	22.6	20.2	16.9	13.7	11.3	8.1	6.5	4.8
82.5°	16.1	16.1	15.3	13.7	12.1	9.6	8.1	5.6	4.1	3.2	2.4
85°	8.1	8.9	8.1	7.2	5.6	4.8	4.1	2.4	1.6	0.8	0.8
87.5°	3.2	3.2	3.2	2.4	2.4	1.6	0.8	0.8	0.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583737

CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9	594.9
2.5°	592.5	592.5	590.8	590.1	589.2	588.4	587.7	586.8	586.8	587.7
5°	587.7	586.0	582.7	582.0	579.6	578.8	577.1	576.4	577.1	576.4
7.5°	580.3	577.1	573.1	571.6	568.3	566.6	564.2	564.2	562.7	563.4
10°	570.7	565.9	561.0	557.8	555.3	552.9	551.4	549.7	549.0	549.0
12.5°	558.6	552.9	548.1	543.3	539.2	537.7	534.4	534.4	532.8	532.0
15°	544.9	537.7	532.0	527.2	524.0	520.7	518.3	516.7	515.1	515.1
17.5°	527.2	520.7	515.1	509.4	504.6	502.2	499.8	497.4	497.4	495.7
20°	507.8	500.5	495.7	490.1	486.1	482.0	478.8	478.8	477.2	478.0
22.5°	486.1	477.2	472.4	468.3	464.3	461.1	457.8	457.8	457.0	456.3
25°	461.9	454.6	448.9	444.1	441.7	438.5	437.6	436.1	435.2	435.2
27.5°	436.1	430.4	423.2	420.8	417.6	415.9	415.9	415.2	413.5	414.3
30°	408.7	402.2	398.2	396.5	393.4	393.4	392.6	390.9	390.9	391.7
32.5°	382.1	375.6	372.4	371.5	368.4	368.4	367.6	368.4	368.4	369.1
35°	353.0	347.4	346.7	344.1	343.4	343.4	343.4	345.0	346.7	344.1
37.5°	325.6	321.7	319.3	318.4	319.3	319.3	320.0	322.4	321.7	320.8
40°	297.5	294.2	292.6	292.6	294.2	295.8	295.8	298.2	299.1	298.2
42.5°	269.2	266.8	266.8	267.6	269.2	270.1	272.5	274.9	275.6	276.5
45°	242.6	242.6	242.6	243.4	244.2	245.8	249.1	251.5	252.3	253.1
47.5°	216.8	216.0	218.4	219.2	221.6	222.5	224.9	228.1	228.9	229.7
50°	192.7	194.2	195.1	197.5	199.1	199.1	202.3	204.0	206.4	206.4
52.5°	170.1	172.5	173.3	175.7	176.6	177.3	179.0	181.4	182.9	182.9
55°	149.9	150.7	152.3	153.1	155.5	156.4	157.9	158.8	161.2	160.3
56°	141.1	142.7	143.5	145.1	146.6	147.5	149.2	149.9	151.6	152.3
57°	132.9	133.8	136.2	137.0	138.6	138.6	139.4	141.8	141.8	142.7
58°	124.9	126.6	127.4	128.1	129.8	130.5	132.2	132.9	133.8	132.9
59°	117.7	118.5	119.2	119.2	120.9	120.9	123.3	124.9	125.7	125.7
60°	110.5	110.5	111.2	112.0	113.7	114.4	114.4	116.1	116.1	116.1
61°	103.1	103.1	104.0	104.8	105.5	105.5	107.2	107.2	108.1	108.8
62°	96.8	95.9	95.9	96.8	96.8	98.3	99.2	100.0	100.7	100.0
63°	89.4	88.7	88.7	88.7	88.7	90.3	90.3	91.1	92.7	91.8
64°	81.4	81.4	81.4	81.4	82.2	82.2	83.8	84.6	85.5	86.3
65°	75.7	74.2	73.3	73.3	74.2	75.0	75.7	76.6	77.4	77.4
66°	69.4	67.7	67.0	67.0	67.0	67.0	68.5	68.5	70.1	70.1
67°	62.0	60.5	59.6	58.9	58.9	58.9	61.3	60.5	60.5	60.5
67.5°	59.6	57.2	56.4	55.7	54.8	56.4	55.7	56.4	56.4	55.7
68°	56.4	54.8	53.2	51.6	51.6	51.6	52.4	53.2	52.4	51.6
69°	50.0	49.2	46.8	45.2	44.4	45.2	44.4	45.2	44.4	45.2
70°	44.4	41.9	39.5	38.7	37.9	37.9	37.9	37.0	37.9	37.0
71°	38.7	36.3	33.9	32.2	31.5	31.5	30.7	31.5	30.7	31.5
72°	33.1	30.7	27.4	25.8	25.8	25.8	25.8	25.0	25.8	25.0
72.5°	30.7	27.4	25.0	23.3	22.6	22.6	22.6	22.6	21.8	22.6
73°	28.2	25.0	21.8	20.9	20.9	20.9	20.2	19.4	20.2	20.2



TEST NUMBER: P583737
CATALOG NUMBER: HCC8S10D010SL-HM80520835-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	9.6	7.2	6.5	6.5	6.5	6.5	6.5	6.5	5.6	5.6
80°	4.1	3.2	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	52.4	52.4	50.7	48.3	44.4	40.3	37.0	33.9	29.8	25.8	24.2
75°	48.3	47.6	45.9	43.5	40.3	36.3	33.1	29.0	25.8	21.8	20.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	23.3	19.4	17.8	16.1	16.1	16.1	15.3	15.3	15.3	16.1
75°	18.5	15.3	13.7	12.1	12.9	12.1	12.9	12.1	12.1	12.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)