

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583731

Luminaire Tested: **HCC8S10D010BZ-HM80520835-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583731  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010BZ-HM80520835-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1193.3 lumens  
Efficiency: N/A  
Efficacy: 120.5 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583731  
CATALOG NUMBER: HCC8S10D010BZ-HM80520835-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583731

CATALOG NUMBER: HCC8S10D010BZ-HM80520835-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59		
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54		
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50		
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	30516
5°	29685
10°	27930
15°	26446
20°	25438
25°	24457
30°	21720
35°	13834
40°	7721
45°	6467
50°	5833
55°	5500
60°	5020
65°	4524
70°	4003
75°	3550
80°	3143
85°	2866



TEST NUMBER: P583731  
 CATALOG NUMBER: HCC8S10D010BZ-HM80520835-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.4	7.5
10°-20°	233.6	19.6
20°-30°	325.9	27.3
30°-40°	234.5	19.7
40°-50°	116.2	9.7
50°-60°	90.9	7.6
60°-70°	61.5	5.2
70°-80°	31.9	2.7
80°-90°	9.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	648.9	54.4
0°-40°	883.5	74.0
0°-60°	1090.6	91.4
0°-90°	1193.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1193.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	990	
5°	959	89
15°	828	234
25°	719	326
35°	368	235
45°	148	116
55°	102	91
65°	62	62
75°	30	32
85°	8	9
90°	0	



TEST NUMBER: P583731  
CATALOG NUMBER: HCC8S10D010BZ-HM80520835-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	989.6
2.5°	980.7
5°	959.0
7.5°	928.3
10°	892.0
12.5°	858.2
15°	828.4
17.5°	800.2
20°	775.2
22.5°	750.2
25°	718.8
27.5°	673.7
30°	610.0
32.5°	510.1
35°	367.5
37.5°	250.6
40°	191.8
42.5°	165.2
45°	148.3
47.5°	133.8
50°	121.6
52.5°	111.2
55°	102.3
57.5°	91.8
60°	81.4
62.5°	70.9
65°	62.0
67.5°	53.1
70°	44.4
72.5°	37.0
75°	29.8
77.5°	23.3
80°	17.7
82.5°	12.9
85°	8.1
87.5°	4.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)