

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583734

Luminaire Tested: **HCC8S10D010MB-HM80520835-81NDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583734  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010MB-HM80520835-81NDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1078.9 lumens  
Efficiency: N/A  
Efficacy: 109.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583734  
CATALOG NUMBER: HCC8S10D010MB-HM80520835-81NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583734  
 CATALOG NUMBER: HCC8S10D010MB-HM80520835-81NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26895
5°	26822
10°	26371
15°	25989
20°	25366
25°	24079
30°	19858
35°	10228
40°	6847
45°	5870
50°	5061
55°	4419
60°	3929
65°	3524
70°	3201
75°	2883
80°	2575
85°	2547



TEST NUMBER: P583734  
 CATALOG NUMBER: HCC8S10D010MB-HM80520835-81NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.9	7.6
10°-20°	229.0	21.2
20°-30°	317.3	29.4
30°-40°	190.6	17.7
40°-50°	104.3	9.7
50°-60°	74.1	6.9
60°-70°	48.1	4.5
70°-80°	25.7	2.4
80°-90°	7.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.3	58.2
0°-40°	818.9	75.9
0°-60°	997.4	92.4
0°-90°	1078.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1078.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	872	
5°	866	82
15°	814	229
25°	708	317
35°	272	191
45°	135	104
55°	82	74
65°	48	48
75°	24	26
85°	7	8
90°	0	



TEST NUMBER: P583734

CATALOG NUMBER: HCC8S10D010MB-HM80520835-81NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	872.2
2.5°	870.5
5°	866.5
7.5°	856.8
10°	842.2
12.5°	828.5
15°	814.1
17.5°	795.6
20°	773.0
22.5°	745.6
25°	707.7
27.5°	648.0
30°	557.7
32.5°	408.7
35°	271.7
37.5°	200.7
40°	170.1
42.5°	150.7
45°	134.6
47.5°	119.2
50°	105.5
52.5°	92.7
55°	82.2
57.5°	72.6
60°	63.7
62.5°	55.7
65°	48.3
67.5°	41.1
70°	35.5
72.5°	29.0
75°	24.2
77.5°	19.4
80°	14.5
82.5°	10.5
85°	7.2
87.5°	3.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)