

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583759

Luminaire Tested: **HCC8S10D010SL-HM80520840-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010SL-HM80520840-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1425.8 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583759
CATALOG NUMBER: HCC8S10D010SL-HM80520840-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583759

CATALOG NUMBER: HCC8S10D010SL-HM80520840-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25042
5°	24869
10°	24802
15°	25453
20°	27555
25°	29543
30°	28884
35°	24051
40°	14777
45°	10231
50°	7810
55°	5118
60°	3201
65°	2401
70°	2416
75°	2776
80°	3072
85°	2760



TEST NUMBER: P583759
 CATALOG NUMBER: HCC8S10D010SL-HM80520840-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	5.4
10°-20°	228.9	16.1
20°-30°	394.0	27.6
30°-40°	381.8	26.8
40°-50°	188.1	13.2
50°-60°	88.7	6.2
60°-70°	35.0	2.5
70°-80°	24.1	1.7
80°-90°	9.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.2	49.0
0°-40°	1081.0	75.8
0°-60°	1357.8	95.2
0°-90°	1425.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1425.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	812	
5°	803	76
15°	797	229
25°	868	394
35°	639	382
45°	235	188
55°	95	89
65°	33	35
75°	23	24
85°	8	9
90°	0	



TEST NUMBER: P583759
CATALOG NUMBER: HCC8S10D010SL-HM80520840-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	812.1
2.5°	809.4
5°	803.4
7.5°	797.3
10°	792.1
12.5°	791.3
15°	797.3
17.5°	815.6
20°	839.7
22.5°	861.4
25°	868.3
27.5°	852.7
30°	811.2
32.5°	742.8
35°	638.9
37.5°	496.1
40°	367.1
42.5°	284.9
45°	234.6
47.5°	197.4
50°	162.8
52.5°	128.1
55°	95.2
57.5°	69.2
60°	51.9
62.5°	40.7
65°	32.9
67.5°	28.6
70°	26.8
72.5°	25.1
75°	23.3
77.5°	20.8
80°	17.3
82.5°	13.0
85°	7.8
87.5°	3.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)