

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583748

Luminaire Tested: **HCC8W10D010MW-HM80520840-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583748  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MW-HM80520840-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1282.1 lumens  
Efficiency: N/A  
Efficacy: 129.5 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583748  
CATALOG NUMBER: HCC8W10D010MW-HM80520840-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583748  
 CATALOG NUMBER: HCC8W10D010MW-HM80520840-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	32785
5°	31889
10°	30009
15°	28412
20°	27332
25°	26277
30°	23333
35°	14858
40°	8292
45°	6947
50°	6275
55°	5914
60°	5390
65°	4867
70°	4292
75°	3813
80°	3374
85°	3078



TEST NUMBER: P583748  
 CATALOG NUMBER: HCC8W10D010MW-HM80520840-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	7.5
10°-20°	251.0	19.6
20°-30°	350.2	27.3
30°-40°	251.9	19.6
40°-50°	124.9	9.7
50°-60°	97.7	7.6
60°-70°	66.1	5.2
70°-80°	34.3	2.7
80°-90°	9.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.2	54.4
0°-40°	949.1	74.0
0°-60°	1171.7	91.4
0°-90°	1282.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1282.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1063	
5°	1030	96
15°	890	251
25°	772	350
35°	395	252
45°	159	125
55°	110	98
65°	67	66
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P583748  
CATALOG NUMBER: HCC8W10D010MW-HM80520840-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1063.2
2.5°	1053.7
5°	1030.2
7.5°	997.3
10°	958.4
12.5°	922.1
15°	890.0
17.5°	859.7
20°	832.9
22.5°	806.1
25°	772.3
27.5°	723.7
30°	655.3
32.5°	548.0
35°	394.7
37.5°	269.2
40°	206.0
42.5°	177.5
45°	159.3
47.5°	143.8
50°	130.8
52.5°	119.5
55°	110.0
57.5°	98.7
60°	87.4
62.5°	76.2
65°	66.7
67.5°	57.1
70°	47.6
72.5°	39.8
75°	32.0
77.5°	25.1
80°	19.0
82.5°	13.8
85°	8.7
87.5°	4.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)