

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593525

Luminaire Tested: **HCC8W10D010BZ-HM80520850-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010BZ-HM80520850-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1159.1 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593525
CATALOG NUMBER: HCC8W10D010BZ-HM80520850-81NDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593525

CATALOG NUMBER: HCC8W10D010BZ-HM80520850-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28894
5°	28815
10°	28337
15°	27924
20°	27253
25°	25872
30°	21339
35°	10985
40°	7354
45°	6306
50°	5445
55°	4747
60°	4218
65°	3787
70°	3435
75°	3098
80°	2770
85°	2760



TEST NUMBER: P593525
 CATALOG NUMBER: HCC8W10D010BZ-HM80520850-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.0	7.6
10°-20°	246.1	21.2
20°-30°	341.0	29.4
30°-40°	204.8	17.7
40°-50°	112.1	9.7
50°-60°	79.6	6.9
60°-70°	51.7	4.5
70°-80°	27.6	2.4
80°-90°	8.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.1	58.2
0°-40°	879.8	75.9
0°-60°	1071.6	92.4
0°-90°	1159.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	937	
5°	931	88
15°	875	246
25°	760	341
35°	292	205
45°	145	112
55°	88	80
65°	52	52
75°	26	28
85°	8	8
90°	0	



TEST NUMBER: P593525
CATALOG NUMBER: HCC8W10D010BZ-HM80520850-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	937.0
2.5°	935.3
5°	930.9
7.5°	920.5
10°	905.0
12.5°	890.2
15°	874.7
17.5°	854.7
20°	830.5
22.5°	801.0
25°	760.4
27.5°	696.2
30°	599.3
32.5°	439.1
35°	291.8
37.5°	215.6
40°	182.7
42.5°	161.9
45°	144.6
47.5°	128.1
50°	113.5
52.5°	99.6
55°	88.3
57.5°	77.9
60°	68.4
62.5°	59.7
65°	51.9
67.5°	44.1
70°	38.1
72.5°	31.1
75°	26.0
77.5°	20.8
80°	15.6
82.5°	11.3
85°	7.8
87.5°	3.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)