

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583765

Luminaire Tested: **HCC8W10D010MW-HM80520927-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010MW-HM80520927-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 936.4 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583765
CATALOG NUMBER: HCC8W10D010MW-HM80520927-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583765

CATALOG NUMBER: HCC8W10D010MW-HM80520927-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54	54	54	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50	50	50	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46	46	46	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	43	43	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40	40	40	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23944
5°	23293
10°	21918
15°	20751
20°	19962
25°	19193
30°	17041
35°	10857
40°	6058
45°	5076
50°	4577
55°	4317
60°	3935
65°	3553
70°	3129
75°	2788
80°	2468
85°	2264



TEST NUMBER: P583765
 CATALOG NUMBER: HCC8W10D010MW-HM80520927-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.1	7.5
10°-20°	183.3	19.6
20°-30°	255.7	27.3
30°-40°	184.0	19.7
40°-50°	91.2	9.7
50°-60°	71.3	7.6
60°-70°	48.3	5.2
70°-80°	25.1	2.7
80°-90°	7.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	509.2	54.4
0°-40°	693.3	74.0
0°-60°	855.8	91.4
0°-90°	936.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	776	
5°	752	70
15°	650	183
25°	564	256
35°	288	184
45°	116	91
55°	80	71
65°	49	48
75°	23	25
85°	6	7
90°	0	



TEST NUMBER: P583765
CATALOG NUMBER: HCC8W10D010MW-HM80520927-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	776.5
2.5°	769.5
5°	752.5
7.5°	728.4
10°	700.0
12.5°	673.5
15°	650.0
17.5°	627.9
20°	608.3
22.5°	588.7
25°	564.1
27.5°	528.6
30°	478.6
32.5°	400.3
35°	288.4
37.5°	196.6
40°	150.5
42.5°	129.6
45°	116.4
47.5°	104.9
50°	95.4
52.5°	87.3
55°	80.3
57.5°	72.1
60°	63.8
62.5°	55.7
65°	48.7
67.5°	41.7
70°	34.7
72.5°	29.1
75°	23.4
77.5°	18.4
80°	13.9
82.5°	10.1
85°	6.4
87.5°	3.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)