

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583798

Luminaire Tested: **HCC8W10D010MW-HM80520935-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583798  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MW-HM80520935-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1092.2 lumens  
Efficiency: N/A  
Efficacy: 110.3 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583798  
CATALOG NUMBER: HCC8W10D010MW-HM80520935-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P583798  
 CATALOG NUMBER: HCC8W10D010MW-HM80520935-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	91	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74	70	67	66
7	84	75	69	65	82	74	68	64	73	68	64		71	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57		64	60	56		63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53		61	56	53		60	56	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49952
5°	45518
10°	38893
15°	33916
20°	30229
25°	26818
30°	21955
35°	12607
40°	5595
45°	3253
50°	1881
55°	1075
60°	592
65°	379
70°	270
75°	167
80°	124
85°	248



TEST NUMBER: P583798  
 CATALOG NUMBER: HCC8W10D010MW-HM80520935-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.1	12.2
10°-20°	298.6	27.3
20°-30°	357.5	32.7
30°-40°	216.3	19.8
40°-50°	60.6	5.5
50°-60°	18.8	1.7
60°-70°	5.4	0.5
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.2	72.3
0°-40°	1005.5	92.1
0°-60°	1084.9	99.3
0°-90°	1092.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1620	
5°	1470	133
15°	1062	299
25°	788	357
35°	335	216
45°	75	61
55°	20	19
65°	5	5
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P583798  
CATALOG NUMBER: HCC8W10D010MW-HM80520935-81MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1619.9
2.5°	1574.0
5°	1470.5
7.5°	1353.7
10°	1242.1
12.5°	1144.5
15°	1062.4
17.5°	990.0
20°	921.2
22.5°	857.6
25°	788.2
27.5°	709.8
30°	616.6
32.5°	496.1
35°	334.9
37.5°	208.5
40°	139.0
42.5°	99.8
45°	74.6
47.5°	54.7
50°	39.2
52.5°	27.4
55°	20.0
57.5°	13.3
60°	9.6
62.5°	6.6
65°	5.2
67.5°	3.7
70°	3.0
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)