

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583799

Luminaire Tested: **HCC8W10D010BZ-HM80520935-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010BZ-HM80520935-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1095.2 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583799
CATALOG NUMBER: HCC8W10D010BZ-HM80520935-81MDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583799

CATALOG NUMBER: HCC8W10D010BZ-HM80520935-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59		
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54		
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50		
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28002
5°	27243
10°	25635
15°	24272
20°	23348
25°	22446
30°	19936
35°	12697
40°	7085
45°	5935
50°	5359
55°	5048
60°	4601
65°	4159
70°	3660
75°	3265
80°	2877
85°	2654



TEST NUMBER: P583799
 CATALOG NUMBER: HCC8W10D010BZ-HM80520935-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.0	7.5
10°-20°	214.4	19.6
20°-30°	299.1	27.3
30°-40°	215.2	19.7
40°-50°	106.7	9.7
50°-60°	83.4	7.6
60°-70°	56.5	5.2
70°-80°	29.3	2.7
80°-90°	8.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.6	54.4
0°-40°	810.8	74.0
0°-60°	1000.9	91.4
0°-90°	1095.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1095.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	908	
5°	880	82
15°	760	214
25°	660	299
35°	337	215
45°	136	107
55°	94	83
65°	57	56
75°	27	29
85°	8	8
90°	0	



TEST NUMBER: P583799

CATALOG NUMBER: HCC8W10D010BZ-HM80520935-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	908.1
2.5°	900.1
5°	880.1
7.5°	852.0
10°	818.7
12.5°	787.7
15°	760.3
17.5°	734.4
20°	711.5
22.5°	688.5
25°	659.7
27.5°	618.3
30°	559.9
32.5°	468.2
35°	337.3
37.5°	229.9
40°	176.0
42.5°	151.6
45°	136.1
47.5°	122.7
50°	111.7
52.5°	102.0
55°	93.9
57.5°	84.3
60°	74.6
62.5°	65.0
65°	57.0
67.5°	48.8
70°	40.6
72.5°	34.0
75°	27.4
77.5°	21.4
80°	16.2
82.5°	11.8
85°	7.5
87.5°	3.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)