

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593533

Luminaire Tested: **HCC8W10D010MB-HM80520950-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MB-HM80520950-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1140.7 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593533  
CATALOG NUMBER: HCC8W10D010MB-HM80520950-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P593533

CATALOG NUMBER: HCC8W10D010MB-HM80520950-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21373
5°	21194
10°	20916
15°	21156
20°	22843
25°	24981
30°	24679
35°	20471
40°	12048
45°	7871
50°	6102
55°	4054
60°	1974
65°	613
70°	207
75°	191
80°	124
85°	248



TEST NUMBER: P593533  
 CATALOG NUMBER: HCC8W10D010MB-HM80520950-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.8	5.7
10°-20°	190.4	16.7
20°-30°	332.8	29.2
30°-40°	323.8	28.4
40°-50°	147.2	12.9
50°-60°	68.3	6.0
60°-70°	11.4	1.0
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	588.0	51.6
0°-40°	911.8	79.9
0°-60°	1127.3	98.8
0°-90°	1140.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1140.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	693	
5°	685	65
15°	663	190
25°	734	333
35°	544	324
45°	180	147
55°	75	68
65°	8	11
75°	2	1
85°	1	0
90°	0	



TEST NUMBER: P593533  
CATALOG NUMBER: HCC8W10D010MB-HM80520950-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	693.1
2.5°	691.5
5°	684.7
7.5°	677.1
10°	668.0
12.5°	661.1
15°	662.7
17.5°	674.8
20°	696.1
22.5°	720.5
25°	734.2
27.5°	726.6
30°	693.1
32.5°	634.4
35°	543.8
37.5°	418.9
40°	299.3
42.5°	223.2
45°	180.5
47.5°	152.3
50°	127.2
52.5°	101.3
55°	75.4
57.5°	51.8
60°	32.0
62.5°	17.5
65°	8.4
67.5°	3.8
70°	2.3
72.5°	1.6
75°	1.6
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)