

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583844

Luminaire Tested: **HCC8W15D010SL-HM80520827-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010SL-HM80520827-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1760.6 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583844
CATALOG NUMBER: HCC8W15D010SL-HM80520827-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583844

CATALOG NUMBER: HCC8W15D010SL-HM80520827-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90	90	90	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81	81	81	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73	73	73	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65	65	65	65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54	54	54	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49	49	49	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45	45	45	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41	41	41	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38	38	38	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30923
5°	30710
10°	30629
15°	31432
20°	34029
25°	36481
30°	35667
35°	29698
40°	18247
45°	12634
50°	9643
55°	6322
60°	3953
65°	2962
70°	2984
75°	3443
80°	3782
85°	3397



TEST NUMBER: P583844
 CATALOG NUMBER: HCC8W15D010SL-HM80520827-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	5.4
10°-20°	282.6	16.1
20°-30°	486.6	27.6
30°-40°	471.4	26.8
40°-50°	232.2	13.2
50°-60°	109.6	6.2
60°-70°	43.2	2.5
70°-80°	29.8	1.7
80°-90°	11.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	863.5	49.0
0°-40°	1334.9	75.8
0°-60°	1676.6	95.2
0°-90°	1760.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1760.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1003	
5°	992	94
15°	985	283
25°	1072	487
35°	789	471
45°	290	232
55°	118	110
65°	41	43
75°	29	30
85°	10	11
90°	0	



TEST NUMBER: P583844
CATALOG NUMBER: HCC8W15D010SL-HM80520827-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1002.8
2.5°	999.5
5°	992.1
7.5°	984.6
10°	978.2
12.5°	977.1
15°	984.6
17.5°	1007.0
20°	1037.0
22.5°	1063.7
25°	1072.2
27.5°	1053.0
30°	1001.7
32.5°	917.2
35°	788.9
37.5°	612.5
40°	453.3
42.5°	351.7
45°	289.7
47.5°	243.8
50°	201.0
52.5°	158.2
55°	117.6
57.5°	85.6
60°	64.1
62.5°	50.2
65°	40.6
67.5°	35.3
70°	33.1
72.5°	31.0
75°	28.9
77.5°	25.7
80°	21.3
82.5°	16.0
85°	9.6
87.5°	4.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)