

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583874

Luminaire Tested: **HCC8W15D010BZ-HM80520835-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010BZ-HM80520835-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1656.9 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583874
CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81WDBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583874

CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92	
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83	
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75	
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62	
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56	
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47	
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31046
5°	30787
10°	30382
15°	30730
20°	33183
25°	36287
30°	35849
35°	29735
40°	17502
45°	11434
50°	8861
55°	5887
60°	2868
65°	890
70°	307
75°	262
80°	195
85°	389



TEST NUMBER: P583874
 CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	5.7
10°-20°	276.5	16.7
20°-30°	483.5	29.2
30°-40°	470.3	28.4
40°-50°	213.8	12.9
50°-60°	99.1	6.0
60°-70°	16.6	1.0
70°-80°	2.0	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.2	51.6
0°-40°	1324.5	79.9
0°-60°	1637.5	98.8
0°-90°	1656.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1656.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1007	
5°	995	94
15°	963	277
25°	1066	483
35°	790	470
45°	262	214
55°	110	99
65°	12	17
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P583874
CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1006.8
2.5°	1004.5
5°	994.6
7.5°	983.5
10°	970.3
12.5°	960.3
15°	962.6
17.5°	980.1
20°	1011.2
22.5°	1046.5
25°	1066.5
27.5°	1055.5
30°	1006.8
32.5°	921.6
35°	789.9
37.5°	608.5
40°	434.8
42.5°	324.1
45°	262.2
47.5°	221.2
50°	184.7
52.5°	147.1
55°	109.5
57.5°	75.2
60°	46.5
62.5°	25.4
65°	12.2
67.5°	5.5
70°	3.4
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)