

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583867

Luminaire Tested: **HCC8S15D010MW-HM80520835-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583867  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S15D010MW-HM80520835-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1638.2 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583867  
CATALOG NUMBER: HCC8S15D010MW-HM80520835-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583867  
 CATALOG NUMBER: HCC8S15D010MW-HM80520835-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92		90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82		80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74		72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67		65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61		59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56		54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52		50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48		46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45		43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42		40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41888
5°	40745
10°	38342
15°	36304
20°	34919
25°	33572
30°	29817
35°	18988
40°	10599
45°	8874
50°	8011
55°	7553
60°	6889
65°	6217
70°	5491
75°	4885
80°	4315
85°	3927



TEST NUMBER: P583867  
 CATALOG NUMBER: HCC8S15D010MW-HM80520835-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.7	7.5
10°-20°	320.7	19.6
20°-30°	447.4	27.3
30°-40°	321.9	19.7
40°-50°	159.5	9.7
50°-60°	124.8	7.6
60°-70°	84.5	5.2
70°-80°	43.9	2.7
80°-90°	12.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.8	54.4
0°-40°	1212.7	74.0
0°-60°	1497.1	91.4
0°-90°	1638.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1638.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1358	
5°	1316	123
15°	1137	321
25°	987	447
35°	504	322
45°	204	160
55°	140	125
65°	85	85
75°	41	44
85°	11	13
90°	0	



TEST NUMBER: P583867  
CATALOG NUMBER: HCC8S15D010MW-HM80520835-81MDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1358.4
2.5°	1346.2
5°	1316.3
7.5°	1274.3
10°	1224.5
12.5°	1178.0
15°	1137.2
17.5°	1098.4
20°	1064.1
22.5°	1029.8
25°	986.7
27.5°	924.7
30°	837.4
32.5°	700.2
35°	504.4
37.5°	344.0
40°	263.3
42.5°	226.8
45°	203.5
47.5°	183.6
50°	167.0
52.5°	152.7
55°	140.5
57.5°	126.0
60°	111.7
62.5°	97.4
65°	85.2
67.5°	73.0
70°	60.9
72.5°	50.9
75°	41.0
77.5°	32.1
80°	24.3
82.5°	17.7
85°	11.1
87.5°	5.5
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)