

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593552

Luminaire Tested: **HCC8S15D010BZ-HM80520850-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010BZ-HM80520850-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1755.2 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593552
CATALOG NUMBER: HCC8S15D010BZ-HM80520850-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P593552
 CATALOG NUMBER: HCC8S15D010BZ-HM80520850-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	90	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	56		64	60	56		63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53		61	56	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80273
5°	73148
10°	62499
15°	54501
20°	48577
25°	43092
30°	35283
35°	20260
40°	8993
45°	5233
50°	3022
55°	1726
60°	950
65°	606
70°	424
75°	286
80°	213
85°	425



TEST NUMBER: P593552
 CATALOG NUMBER: HCC8S15D010BZ-HM80520850-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.9	12.2
10°-20°	479.9	27.3
20°-30°	574.4	32.7
30°-40°	347.5	19.8
40°-50°	97.4	5.6
50°-60°	30.2	1.7
60°-70°	8.6	0.5
70°-80°	2.4	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1268.2	72.3
0°-40°	1615.8	92.1
0°-60°	1743.4	99.3
0°-90°	1755.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1755.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2603	
5°	2363	214
15°	1707	480
25°	1266	574
35°	538	348
45°	120	97
55°	32	30
65°	8	9
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P593552
CATALOG NUMBER: HCC8S15D010BZ-HM80520850-81MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2603.2
2.5°	2529.4
5°	2363.1
7.5°	2175.4
10°	1996.0
12.5°	1839.2
15°	1707.2
17.5°	1590.8
20°	1480.3
22.5°	1378.2
25°	1266.5
27.5°	1140.5
30°	990.9
32.5°	797.2
35°	538.2
37.5°	335.0
40°	223.4
42.5°	160.4
45°	120.0
47.5°	88.0
50°	63.0
52.5°	44.0
55°	32.1
57.5°	21.3
60°	15.4
62.5°	10.7
65°	8.3
67.5°	5.9
70°	4.7
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)