

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593551

Luminaire Tested: **HCC8S15D010MB-HM80520850-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593551  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S15D010MB-HM80520850-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1957.3 lumens  
Efficiency: N/A  
Efficacy: 139.8 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593551  
CATALOG NUMBER: HCC8S15D010MB-HM80520850-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P593551  
 CATALOG NUMBER: HCC8S15D010MB-HM80520850-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34373
5°	34136
10°	34049
15°	34941
20°	37826
25°	40557
30°	39648
35°	33014
40°	20284
45°	14047
50°	10717
55°	7027
60°	4397
65°	3298
70°	3327
75°	3824
80°	4209
85°	3786



TEST NUMBER: P593551  
 CATALOG NUMBER: HCC8S15D010MB-HM80520850-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.8	5.4
10°-20°	314.2	16.1
20°-30°	540.9	27.6
30°-40°	524.0	26.8
40°-50°	258.1	13.2
50°-60°	121.8	6.2
60°-70°	48.0	2.5
70°-80°	33.1	1.7
80°-90°	12.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.9	49.0
0°-40°	1483.9	75.8
0°-60°	1863.8	95.2
0°-90°	1957.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1957.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1115	
5°	1103	105
15°	1094	314
25°	1192	541
35°	877	524
45°	322	258
55°	131	122
65°	45	48
75°	32	33
85°	11	12
90°	0	



TEST NUMBER: P593551  
CATALOG NUMBER: HCC8S15D010MB-HM80520850-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1114.7
2.5°	1111.1
5°	1102.8
7.5°	1094.5
10°	1087.4
12.5°	1086.2
15°	1094.5
17.5°	1119.4
20°	1152.7
22.5°	1182.5
25°	1192.0
27.5°	1170.5
30°	1113.5
32.5°	1019.7
35°	877.0
37.5°	680.9
40°	503.9
42.5°	391.0
45°	322.1
47.5°	271.0
50°	223.4
52.5°	175.9
55°	130.7
57.5°	95.1
60°	71.3
62.5°	55.9
65°	45.2
67.5°	39.2
70°	36.9
72.5°	34.5
75°	32.1
77.5°	28.6
80°	23.7
82.5°	17.8
85°	10.7
87.5°	4.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)