

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593561

Luminaire Tested: **HCC8S15D010MW-HM80520850-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593561  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S15D010MW-HM80520850-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1825.3 lumens  
Efficiency: N/A  
Efficacy: 130.4 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593561  
CATALOG NUMBER: HCC8S15D010MW-HM80520850-81WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P593561  
 CATALOG NUMBER: HCC8S15D010MW-HM80520850-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91		89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81		79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72		70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65		63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59		57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54		52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49		48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45		44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42		40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39		37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36492
5°	36448
10°	36090
15°	35656
20°	35322
25°	34926
30°	32958
35°	26837
40°	14830
45°	9895
50°	8774
55°	8242
60°	8135
65°	8063
70°	7294
75°	6517
80°	5700
85°	5024



TEST NUMBER: P593561  
 CATALOG NUMBER: HCC8S15D010MW-HM80520850-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.6	6.1
10°-20°	315.4	17.3
20°-30°	468.6	25.7
30°-40°	422.0	23.1
40°-50°	187.1	10.2
50°-60°	138.5	7.6
60°-70°	107.8	5.9
70°-80°	58.4	3.2
80°-90°	16.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	895.5	49.1
0°-40°	1317.5	72.2
0°-60°	1643.1	90.0
0°-90°	1825.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1825.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1183	
5°	1178	112
15°	1117	315
25°	1026	469
35°	713	422
45°	227	187
55°	153	139
65°	110	108
75°	55	58
85°	14	16
90°	0	



TEST NUMBER: P593561  
CATALOG NUMBER: HCC8S15D010MW-HM80520850-81WDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1183.4
2.5°	1181.0
5°	1177.5
7.5°	1168.0
10°	1152.6
12.5°	1134.7
15°	1116.9
17.5°	1099.1
20°	1076.4
22.5°	1053.9
25°	1026.5
27.5°	985.0
30°	925.6
32.5°	840.0
35°	712.9
37.5°	532.2
40°	368.4
42.5°	272.1
45°	226.9
47.5°	200.8
50°	182.9
52.5°	166.3
55°	153.3
57.5°	142.6
60°	131.9
62.5°	122.4
65°	110.5
67.5°	96.3
70°	80.9
72.5°	67.7
75°	54.7
77.5°	42.8
80°	32.1
82.5°	22.5
85°	14.2
87.5°	5.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)