

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583900

Luminaire Tested: **HCC8W15D010BZ-HM80520927-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010BZ-HM80520927-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1281.9 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583900
CATALOG NUMBER: HCC8W15D010BZ-HM80520927-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P583900
 CATALOG NUMBER: HCC8W15D010BZ-HM80520927-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66																			
7	84	75	69	65	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58																			
9	76	67	61	57	75	66	61	57	65	60	57	64	60	56	63	59	56	55																			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58626
5°	53424
10°	45647
15°	39806
20°	35480
25°	31476
30°	25769
35°	14798
40°	6569
45°	3820
50°	2207
55°	1258
60°	697
65°	438
70°	316
75°	203
80°	142
85°	283



TEST NUMBER: P583900
 CATALOG NUMBER: HCC8W15D010BZ-HM80520927-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.2	12.2
10°-20°	350.5	27.3
20°-30°	419.6	32.7
30°-40°	253.8	19.8
40°-50°	71.1	5.5
50°-60°	22.1	1.7
60°-70°	6.3	0.5
70°-80°	1.7	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.3	72.3
0°-40°	1180.2	92.1
0°-60°	1273.4	99.3
0°-90°	1281.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1281.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1901	
5°	1726	156
15°	1247	351
25°	925	420
35°	393	254
45°	88	71
55°	23	22
65°	6	6
75°	2	2
85°	1	1
90°	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P583900

CATALOG NUMBER: HCC8W15D010BZ-HM80520927-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1901.2
2.5°	1847.5
5°	1725.9
7.5°	1588.9
10°	1457.8
12.5°	1343.3
15°	1246.9
17.5°	1162.0
20°	1081.2
22.5°	1006.7
25°	925.1
27.5°	833.0
30°	723.7
32.5°	582.3
35°	393.1
37.5°	244.7
40°	163.2
42.5°	117.1
45°	87.6
47.5°	64.2
50°	46.0
52.5°	32.1
55°	23.4
57.5°	15.7
60°	11.3
62.5°	7.8
65°	6.0
67.5°	4.3
70°	3.5
72.5°	1.7
75°	1.7
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)