

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583901

Luminaire Tested: **HCC8S15D010BZ-HM80520927-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010BZ-HM80520927-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1285.4 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583901
CATALOG NUMBER: HCC8S15D010BZ-HM80520927-81MDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583901

CATALOG NUMBER: HCC8S15D010BZ-HM80520927-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72				
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65				
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59				
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54				
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50				
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32868
5°	31972
10°	30088
15°	28486
20°	27404
25°	26341
30°	23397
35°	14900
40°	8312
45°	6964
50°	6289
55°	5930
60°	5409
65°	4881
70°	4301
75°	3836
80°	3374
85°	3078



TEST NUMBER: P583901
 CATALOG NUMBER: HCC8S15D010BZ-HM80520927-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.3	7.5
10°-20°	251.7	19.6
20°-30°	351.1	27.3
30°-40°	252.6	19.7
40°-50°	125.2	9.7
50°-60°	98.0	7.6
60°-70°	66.3	5.2
70°-80°	34.4	2.7
80°-90°	9.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.0	54.4
0°-40°	951.6	74.0
0°-60°	1174.8	91.4
0°-90°	1285.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1285.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1066	
5°	1033	96
15°	892	252
25°	774	351
35°	396	253
45°	160	125
55°	110	98
65°	67	66
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P583901
CATALOG NUMBER: HCC8S15D010BZ-HM80520927-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1065.9
2.5°	1056.3
5°	1032.9
7.5°	999.9
10°	960.9
12.5°	924.5
15°	892.3
17.5°	861.9
20°	835.1
22.5°	808.1
25°	774.2
27.5°	725.7
30°	657.1
32.5°	549.5
35°	395.8
37.5°	269.9
40°	206.5
42.5°	178.0
45°	159.7
47.5°	144.1
50°	131.1
52.5°	119.8
55°	110.3
57.5°	98.9
60°	87.7
62.5°	76.4
65°	66.9
67.5°	57.2
70°	47.7
72.5°	39.9
75°	32.2
77.5°	25.2
80°	19.0
82.5°	13.9
85°	8.7
87.5°	4.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)