

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583904

Luminaire Tested: **HCC8S15D010MW-HM80520927-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010MW-HM80520927-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1162.2 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583904
CATALOG NUMBER: HCC8S15D010MW-HM80520927-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P583904

CATALOG NUMBER: HCC8S15D010MW-HM80520927-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90	
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			81	
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			73	
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			67	
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			61	
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56	
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			52	
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48	
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			45	
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28968
5°	28893
10°	28406
15°	27994
20°	27325
25°	25937
30°	21393
35°	11015
40°	7375
45°	6323
50°	5459
55°	4763
60°	4231
65°	3801
70°	3444
75°	3098
80°	2788
85°	2760



TEST NUMBER: P583904
 CATALOG NUMBER: HCC8S15D010MW-HM80520927-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	7.6
10°-20°	246.7	21.2
20°-30°	341.8	29.4
30°-40°	205.3	17.7
40°-50°	112.4	9.7
50°-60°	79.9	6.9
60°-70°	51.8	4.5
70°-80°	27.7	2.4
80°-90°	8.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.8	58.2
0°-40°	882.1	75.9
0°-60°	1074.4	92.4
0°-90°	1162.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1162.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	939	
5°	933	88
15°	877	247
25°	762	342
35°	293	205
45°	145	112
55°	89	80
65°	52	52
75°	26	28
85°	8	8
90°	0	



TEST NUMBER: P583904
CATALOG NUMBER: HCC8S15D010MW-HM80520927-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	939.4
2.5°	937.7
5°	933.4
7.5°	922.9
10°	907.2
12.5°	892.5
15°	876.9
17.5°	857.0
20°	832.7
22.5°	803.1
25°	762.3
27.5°	698.1
30°	600.8
32.5°	440.2
35°	292.6
37.5°	216.2
40°	183.2
42.5°	162.3
45°	145.0
47.5°	128.5
50°	113.8
52.5°	99.9
55°	88.6
57.5°	78.1
60°	68.6
62.5°	59.9
65°	52.1
67.5°	44.2
70°	38.2
72.5°	31.2
75°	26.0
77.5°	20.8
80°	15.7
82.5°	11.3
85°	7.8
87.5°	3.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)