

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583911

Luminaire Tested: **HCC8W15D010MW-HM80520927-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583911  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010MW-HM80520927-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1333.1 lumens  
Efficiency: N/A  
Efficacy: 95.2 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583911  
CATALOG NUMBER: HCC8W15D010MW-HM80520927-81WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583911  
 CATALOG NUMBER: HCC8W15D010MW-HM80520927-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89		
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79		
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26652
5°	26621
10°	26358
15°	26044
20°	25803
25°	25511
30°	24070
35°	19601
40°	10832
45°	7230
50°	6409
55°	6016
60°	5939
65°	5888
70°	5319
75°	4754
80°	4155
85°	3680



TEST NUMBER: P583911  
 CATALOG NUMBER: HCC8W15D010MW-HM80520927-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.5	6.1
10°-20°	230.3	17.3
20°-30°	342.3	25.7
30°-40°	308.2	23.1
40°-50°	136.6	10.2
50°-60°	101.2	7.6
60°-70°	78.7	5.9
70°-80°	42.7	3.2
80°-90°	11.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.1	49.1
0°-40°	962.3	72.2
0°-60°	1200.1	90.0
0°-90°	1333.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1333.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	864	
5°	860	82
15°	816	230
25°	750	342
35°	521	308
45°	166	137
55°	112	101
65°	81	79
75°	40	43
85°	10	12
90°	0	



TEST NUMBER: P583911  
CATALOG NUMBER: HCC8W15D010MW-HM80520927-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	864.3
2.5°	862.7
5°	860.0
7.5°	853.0
10°	841.8
12.5°	828.8
15°	815.8
17.5°	802.8
20°	786.3
22.5°	769.8
25°	749.8
27.5°	719.4
30°	676.0
32.5°	613.6
35°	520.7
37.5°	388.7
40°	269.1
42.5°	198.7
45°	165.8
47.5°	146.6
50°	133.6
52.5°	121.5
55°	111.9
57.5°	104.1
60°	96.3
62.5°	89.4
65°	80.7
67.5°	70.3
70°	59.0
72.5°	49.5
75°	39.9
77.5°	31.2
80°	23.4
82.5°	16.5
85°	10.4
87.5°	4.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)