

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583935

Luminaire Tested: **HCC8W15D010MW-HM80520935-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010MW-HM80520935-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1503.4 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583935
CATALOG NUMBER: HCC8W15D010MW-HM80520935-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583935

CATALOG NUMBER: HCC8W15D010MW-HM80520935-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72				
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65				
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59				
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54				
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50				
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38444
5°	37393
10°	35188
15°	33319
20°	32051
25°	30812
30°	27364
35°	17429
40°	9725
45°	8146
50°	7354
55°	6930
60°	6321
65°	5706
70°	5031
75°	4480
80°	3960
85°	3573



TEST NUMBER: P583935
 CATALOG NUMBER: HCC8W15D010MW-HM80520935-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.6	7.5
10°-20°	294.3	19.6
20°-30°	410.6	27.3
30°-40°	295.5	19.7
40°-50°	146.4	9.7
50°-60°	114.5	7.6
60°-70°	77.5	5.2
70°-80°	40.3	2.7
80°-90°	11.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.6	54.4
0°-40°	1113.0	74.0
0°-60°	1374.0	91.4
0°-90°	1503.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1503.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1247	
5°	1208	113
15°	1044	294
25°	906	411
35°	463	295
45°	187	146
55°	129	115
65°	78	78
75°	38	40
85°	10	12
90°	0	



TEST NUMBER: P583935
CATALOG NUMBER: HCC8W15D010MW-HM80520935-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1246.7
2.5°	1235.5
5°	1208.0
7.5°	1169.5
10°	1123.8
12.5°	1081.1
15°	1043.7
17.5°	1008.1
20°	976.7
22.5°	945.1
25°	905.6
27.5°	848.7
30°	768.5
32.5°	642.6
35°	463.0
37.5°	315.7
40°	241.6
42.5°	208.1
45°	186.8
47.5°	168.6
50°	153.3
52.5°	140.1
55°	128.9
57.5°	115.7
60°	102.5
62.5°	89.3
65°	78.2
67.5°	67.0
70°	55.8
72.5°	46.8
75°	37.6
77.5°	29.4
80°	22.3
82.5°	16.3
85°	10.1
87.5°	5.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)