

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583960

Luminaire Tested: **HCC8S15D010MW-HM80520940-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583960  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S15D010MW-HM80520940-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1756.1 lumens  
Efficiency: N/A  
Efficacy: 125.4 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583960  
CATALOG NUMBER: HCC8S15D010MW-HM80520940-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583960  
 CATALOG NUMBER: HCC8S15D010MW-HM80520940-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42129
5°	40996
10°	40687
15°	40081
20°	38866
25°	37416
30°	34952
35°	28922
40°	17462
45°	11761
50°	8477
55°	4833
60°	2128
65°	766
70°	279
75°	131
80°	0
85°	0



TEST NUMBER: P583960  
 CATALOG NUMBER: HCC8S15D010MW-HM80520940-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.8	7.2
10°-20°	352.8	20.1
20°-30°	503.3	28.7
30°-40°	458.3	26.1
40°-50°	216.2	12.3
50°-60°	85.0	4.8
60°-70°	13.6	0.8
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.0	55.9
0°-40°	1440.3	82.0
0°-60°	1741.5	99.2
0°-90°	1756.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1756.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1366	
5°	1324	126
15°	1256	353
25°	1100	503
35°	768	458
45°	270	216
55°	90	85
65°	10	14
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583960  
CATALOG NUMBER: HCC8S15D010MW-HM80520940-81WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1366.2
2.5°	1348.5
5°	1324.4
7.5°	1310.9
10°	1299.4
12.5°	1280.6
15°	1255.5
17.5°	1224.2
20°	1184.4
22.5°	1142.6
25°	1099.7
27.5°	1047.4
30°	981.6
32.5°	892.8
35°	768.3
37.5°	593.7
40°	433.8
42.5°	333.4
45°	269.7
47.5°	221.6
50°	176.7
52.5°	132.8
55°	89.9
57.5°	56.4
60°	34.5
62.5°	21.0
65°	10.5
67.5°	5.2
70°	3.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)