

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593576

Luminaire Tested: **HCC8W15D010MW-HM80520950-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010MW-HM80520950-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1399.6 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593576
CATALOG NUMBER: HCC8W15D010MW-HM80520950-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P593576

CATALOG NUMBER: HCC8W15D010MW-HM80520950-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90	
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			81	
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			73	
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			67	
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			61	
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56	
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			52	
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48	
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			45	
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34888
5°	34792
10°	34215
15°	33715
20°	32904
25°	31234
30°	25765
35°	13262
40°	8880
45°	7614
50°	6572
55°	5731
60°	5088
65°	4582
70°	4147
75°	3729
80°	3338
85°	3326



TEST NUMBER: P593576
 CATALOG NUMBER: HCC8W15D010MW-HM80520950-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	7.6
10°-20°	297.1	21.2
20°-30°	411.7	29.4
30°-40°	247.3	17.7
40°-50°	135.4	9.7
50°-60°	96.2	6.9
60°-70°	62.5	4.5
70°-80°	33.3	2.4
80°-90°	10.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	815.1	58.2
0°-40°	1062.3	75.9
0°-60°	1293.8	92.4
0°-90°	1399.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1399.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1131	
5°	1124	106
15°	1056	297
25°	918	412
35°	352	247
45°	175	135
55°	107	96
65°	63	62
75°	31	33
85°	9	10
90°	0	



TEST NUMBER: P593576
CATALOG NUMBER: HCC8W15D010MW-HM80520950-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1131.4
2.5°	1129.2
5°	1124.0
7.5°	1111.5
10°	1092.7
12.5°	1074.9
15°	1056.1
17.5°	1032.0
20°	1002.7
22.5°	967.1
25°	918.0
27.5°	840.6
30°	723.6
32.5°	530.1
35°	352.3
37.5°	260.4
40°	220.6
42.5°	195.6
45°	174.6
47.5°	154.7
50°	137.0
52.5°	120.3
55°	106.6
57.5°	94.1
60°	82.5
62.5°	72.2
65°	62.8
67.5°	53.4
70°	46.0
72.5°	37.6
75°	31.3
77.5°	25.1
80°	18.8
82.5°	13.6
85°	9.4
87.5°	4.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)