

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583967

Luminaire Tested: **HCC8S20D010MB-HM80520827-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583967  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S20D010MB-HM80520827-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2352.6 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583967  
CATALOG NUMBER: HCC8S20D010MB-HM80520827-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583967  
 CATALOG NUMBER: HCC8S20D010MB-HM80520827-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88		92	89	87		90	87	85	84
4	100	93	88	84	98	92	87	83	90	86	82		88	84	82		86	83	81	79
5	95	88	82	78	94	87	82	78	85	81	77		83	80	77		82	79	76	75
6	91	83	78	74	90	82	77	74	81	76	73		79	76	73		78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	65		72	68	65		71	68	65	64
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68	65	62	61
10	77	68	63	59	76	68	63	59	67	62	59		66	62	59		65	62	59	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	140564
5°	134115
10°	115789
15°	88538
20°	67747
25°	53598
30°	40488
35°	21540
40°	8204
45°	3938
50°	1679
55°	704
60°	271
65°	219
70°	126
75°	0
80°	0
85°	0



TEST NUMBER: P583967  
 CATALOG NUMBER: HCC8S20D010MB-HM80520827-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	393.3	16.7
10°-20°	774.3	32.9
20°-30°	721.1	30.7
30°-40°	372.1	15.8
40°-50°	75.8	3.2
50°-60°	13.0	0.6
60°-70°	2.5	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1888.7	80.3
0°-40°	2260.8	96.1
0°-60°	2349.5	99.9
0°-90°	2352.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2352.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4558	
5°	4333	393
15°	2773	774
25°	1575	721
35°	572	372
45°	90	76
55°	13	13
65°	3	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P583967  
CATALOG NUMBER: HCC8S20D010MB-HM80520827-81MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4558.4
2.5°	4497.3
5°	4332.7
7.5°	4061.9
10°	3697.9
12.5°	3220.4
15°	2773.4
17.5°	2386.2
20°	2064.5
22.5°	1802.4
25°	1575.3
27.5°	1359.8
30°	1137.1
32.5°	872.1
35°	572.2
37.5°	331.9
40°	203.8
42.5°	133.9
45°	90.3
47.5°	56.7
50°	35.0
52.5°	20.3
55°	13.1
57.5°	5.8
60°	4.4
62.5°	3.0
65°	3.0
67.5°	1.4
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)