

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583973

Luminaire Tested: **HCC8S20D010SL-HM80520827-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010SL-HM80520827-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2164.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583973
CATALOG NUMBER: HCC8S20D010SL-HM80520827-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583973

CATALOG NUMBER: HCC8S20D010SL-HM80520827-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89	89	89	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79	79	79	79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64	64	64	64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49	49	49	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45	45	45	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50812
5°	50152
10°	48318
15°	46424
20°	45141
25°	43782
30°	39288
35°	25752
40°	14242
45°	11870
50°	10823
55°	10333
60°	9609
65°	8712
70°	7871
75°	7113
80°	6464
85°	6192



TEST NUMBER: P583973
 CATALOG NUMBER: HCC8S20D010SL-HM80520827-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	7.0
10°-20°	410.3	19.0
20°-30°	583.9	27.0
30°-40°	432.1	20.0
40°-50°	214.1	9.9
50°-60°	170.8	7.9
60°-70°	118.6	5.5
70°-80°	63.9	3.0
80°-90°	18.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1146.4	53.0
0°-40°	1578.5	72.9
0°-60°	1963.4	90.7
0°-90°	2164.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2164.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1648	
5°	1620	152
15°	1454	410
25°	1287	584
35°	684	432
45°	272	214
55°	192	171
65°	119	119
75°	60	64
85°	18	19
90°	0	



TEST NUMBER: P583973
CATALOG NUMBER: HCC8S20D010SL-HM80520827-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1647.8
2.5°	1640.6
5°	1620.2
7.5°	1588.1
10°	1543.1
12.5°	1496.4
15°	1454.2
17.5°	1413.6
20°	1375.6
22.5°	1337.8
25°	1286.8
27.5°	1212.6
30°	1103.4
32.5°	936.0
35°	684.1
37.5°	467.2
40°	353.8
42.5°	302.8
45°	272.2
47.5°	247.5
50°	225.6
52.5°	206.7
55°	192.2
57.5°	174.7
60°	155.8
62.5°	136.9
65°	119.4
67.5°	101.9
70°	87.3
72.5°	72.8
75°	59.7
77.5°	48.0
80°	36.4
82.5°	26.2
85°	17.5
87.5°	7.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)