

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583996

Luminaire Tested: **HCC8S20D010BZ-HM80520830-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010BZ-HM80520830-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2224.0 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583996
CATALOG NUMBER: HCC8S20D010BZ-HM80520830-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P583996

CATALOG NUMBER: HCC8S20D010BZ-HM80520830-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44463
5°	44407
10°	43968
15°	43442
20°	43037
25°	42557
30°	40154
35°	32702
40°	18066
45°	12058
50°	10693
55°	10043
60°	9905
65°	9821
70°	8881
75°	7923
80°	6943
85°	6156



TEST NUMBER: P583996
 CATALOG NUMBER: HCC8S20D010BZ-HM80520830-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	6.1
10°-20°	384.2	17.3
20°-30°	570.9	25.7
30°-40°	514.2	23.1
40°-50°	228.0	10.2
50°-60°	168.8	7.6
60°-70°	131.3	5.9
70°-80°	71.2	3.2
80°-90°	19.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1091.1	49.1
0°-40°	1605.3	72.2
0°-60°	2002.1	90.0
0°-90°	2224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1442	
5°	1435	136
15°	1361	384
25°	1251	571
35°	869	514
45°	276	228
55°	187	169
65°	135	131
75°	66	71
85°	17	19
90°	0	



TEST NUMBER: P583996
CATALOG NUMBER: HCC8S20D010BZ-HM80520830-81WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1441.9
2.5°	1439.0
5°	1434.6
7.5°	1423.0
10°	1404.2
12.5°	1382.6
15°	1360.8
17.5°	1339.1
20°	1311.5
22.5°	1284.1
25°	1250.8
27.5°	1200.1
30°	1127.7
32.5°	1023.5
35°	868.7
37.5°	648.6
40°	448.8
42.5°	331.6
45°	276.5
47.5°	244.7
50°	222.9
52.5°	202.7
55°	186.8
57.5°	173.8
60°	160.6
62.5°	149.2
65°	134.6
67.5°	117.3
70°	98.5
72.5°	82.5
75°	66.5
77.5°	52.1
80°	39.1
82.5°	27.5
85°	17.4
87.5°	7.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)