

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583997

Luminaire Tested: **HCC8S20D010MB-HM80520830-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520830-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2384.6 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583997
CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583997
 CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49		
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45		
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41879
5°	41593
10°	41485
15°	42571
20°	46089
25°	49413
30°	48308
35°	40223
40°	24712
45°	17112
50°	13058
55°	8559
60°	5359
65°	4013
70°	4048
75°	4658
80°	5150
85°	4599



TEST NUMBER: P583997
 CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	5.4
10°-20°	382.8	16.1
20°-30°	659.0	27.6
30°-40°	638.5	26.8
40°-50°	314.5	13.2
50°-60°	148.4	6.2
60°-70°	58.5	2.5
70°-80°	40.4	1.7
80°-90°	15.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.5	49.0
0°-40°	1808.0	75.8
0°-60°	2270.8	95.2
0°-90°	2384.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2384.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1358	
5°	1344	128
15°	1334	383
25°	1452	659
35°	1068	638
45°	392	314
55°	159	148
65°	55	58
75°	39	40
85°	13	15
90°	0	



TEST NUMBER: P583997

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1358.1
2.5°	1353.9
5°	1343.7
7.5°	1333.5
10°	1324.9
12.5°	1323.4
15°	1333.5
17.5°	1363.9
20°	1404.5
22.5°	1440.7
25°	1452.3
27.5°	1426.2
30°	1356.7
32.5°	1242.3
35°	1068.5
37.5°	829.6
40°	613.9
42.5°	476.3
45°	392.4
47.5°	330.1
50°	272.2
52.5°	214.3
55°	159.2
57.5°	115.8
60°	86.9
62.5°	68.1
65°	55.0
67.5°	47.8
70°	44.9
72.5°	42.0
75°	39.1
77.5°	34.8
80°	29.0
82.5°	21.7
85°	13.0
87.5°	5.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)