

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584008

Luminaire Tested: **HCC8W20D010BZ-HM80520835-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584008  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W20D010BZ-HM80520835-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2396.4 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584008  
CATALOG NUMBER: HCC8W20D010BZ-HM80520835-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584008

CATALOG NUMBER: HCC8W20D010BZ-HM80520835-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54867
5°	53631
10°	51984
15°	50935
20°	50480
25°	49723
30°	47101
35°	39135
40°	23041
45°	15241
50°	11998
55°	8828
60°	6130
65°	3736
70°	1632
75°	715
80°	533
85°	0



TEST NUMBER: P584008  
 CATALOG NUMBER: HCC8W20D010BZ-HM80520835-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.2	6.8
10°-20°	451.1	18.8
20°-30°	668.3	27.9
30°-40°	617.5	25.8
40°-50°	284.7	11.9
50°-60°	149.7	6.2
60°-70°	52.9	2.2
70°-80°	8.3	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1282.5	53.5
0°-40°	1900.0	79.3
0°-60°	2334.4	97.4
0°-90°	2396.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2396.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1779	
5°	1733	163
15°	1596	451
25°	1461	668
35°	1040	617
45°	350	285
55°	164	150
65°	51	53
75°	6	8
85°	0	1
90°	0	



TEST NUMBER: P584008  
CATALOG NUMBER: HCC8W20D010BZ-HM80520835-81WDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1779.3
2.5°	1764.1
5°	1732.6
7.5°	1697.9
10°	1660.2
12.5°	1624.1
15°	1595.5
17.5°	1569.8
20°	1538.3
22.5°	1503.5
25°	1461.4
27.5°	1404.1
30°	1322.8
32.5°	1206.7
35°	1039.6
37.5°	798.4
40°	572.4
42.5°	429.4
45°	349.5
47.5°	296.8
50°	250.1
52.5°	204.8
55°	164.2
57.5°	129.5
60°	99.4
62.5°	75.3
65°	51.2
67.5°	30.1
70°	18.1
72.5°	10.5
75°	6.0
77.5°	4.5
80°	3.0
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)