

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593588

Luminaire Tested: **HCC8W20D010SL-HM80520850-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010SL-HM80520850-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2574.9 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593588
CATALOG NUMBER: HCC8W20D010SL-HM80520850-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593588
 CATALOG NUMBER: HCC8W20D010SL-HM80520850-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68				
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62				
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57				
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52				
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44				
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58947
5°	57618
10°	55854
15°	54721
20°	54234
25°	53421
30°	50601
35°	42045
40°	24760
45°	16375
50°	12890
55°	9489
60°	6593
65°	4020
70°	1749
75°	774
80°	568
85°	0



TEST NUMBER: P593588
 CATALOG NUMBER: HCC8W20D010SL-HM80520850-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	6.8
10°-20°	484.6	18.8
20°-30°	718.0	27.9
30°-40°	663.5	25.8
40°-50°	305.9	11.9
50°-60°	160.9	6.2
60°-70°	56.9	2.2
70°-80°	8.9	0.3
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1377.9	53.5
0°-40°	2041.3	79.3
0°-60°	2508.2	97.4
0°-90°	2574.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2574.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1912	
5°	1861	175
15°	1714	485
25°	1570	718
35°	1117	663
45°	376	306
55°	176	161
65°	55	57
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P593588

CATALOG NUMBER: HCC8W20D010SL-HM80520850-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1911.6
2.5°	1895.5
5°	1861.4
7.5°	1824.2
10°	1783.8
12.5°	1744.9
15°	1714.1
17.5°	1686.6
20°	1652.7
22.5°	1615.4
25°	1570.1
27.5°	1508.6
30°	1421.1
32.5°	1296.5
35°	1116.9
37.5°	857.9
40°	615.1
42.5°	461.3
45°	375.5
47.5°	318.9
50°	268.7
52.5°	220.1
55°	176.5
57.5°	139.2
60°	106.9
62.5°	81.0
65°	55.1
67.5°	32.4
70°	19.4
72.5°	11.3
75°	6.5
77.5°	4.8
80°	3.2
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)