

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584042

Luminaire Tested: **HCC8S20D010MB-HM80520927-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520927-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1880.6 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584042
CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584042

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43054
5°	42082
10°	40793
15°	39969
20°	39611
25°	39019
30°	36960
35°	30706
40°	18086
45°	11958
50°	9412
55°	6924
60°	4810
65°	2933
70°	1280
75°	560
80°	426
85°	0



TEST NUMBER: P584042
 CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	6.8
10°-20°	354.0	18.8
20°-30°	524.4	27.9
30°-40°	484.6	25.8
40°-50°	223.4	11.9
50°-60°	117.5	6.2
60°-70°	41.5	2.2
70°-80°	6.5	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1006.4	53.5
0°-40°	1491.0	79.3
0°-60°	1831.9	97.4
0°-90°	1880.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1880.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1396	
5°	1360	128
15°	1252	354
25°	1147	524
35°	816	485
45°	274	223
55°	129	118
65°	40	42
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P584042
CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1396.2
2.5°	1384.4
5°	1359.5
7.5°	1332.4
10°	1302.8
12.5°	1274.4
15°	1252.0
17.5°	1231.9
20°	1207.1
22.5°	1179.9
25°	1146.8
27.5°	1101.9
30°	1038.0
32.5°	946.9
35°	815.7
37.5°	626.6
40°	449.3
42.5°	337.0
45°	274.2
47.5°	232.9
50°	196.2
52.5°	160.8
55°	128.8
57.5°	101.7
60°	78.0
62.5°	59.1
65°	40.2
67.5°	23.6
70°	14.2
72.5°	8.3
75°	4.7
77.5°	3.5
80°	2.4
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)