

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584033

Luminaire Tested: **HCC8S20D010MB-HM80520927-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520927-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1750.5 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584033
CATALOG NUMBER: HCC8S20D010MB-HM80520927-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584033

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44762
5°	43543
10°	40975
15°	38794
20°	37318
25°	35878
30°	31861
35°	20290
40°	11323
45°	9485
50°	8563
55°	8070
60°	7364
65°	6640
70°	5860
75°	5207
80°	4617
85°	4175



TEST NUMBER: P584033
 CATALOG NUMBER: HCC8S20D010MB-HM80520927-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	7.5
10°-20°	342.7	19.6
20°-30°	478.1	27.3
30°-40°	344.0	19.7
40°-50°	170.5	9.7
50°-60°	133.4	7.6
60°-70°	90.3	5.2
70°-80°	46.9	2.7
80°-90°	13.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.0	54.4
0°-40°	1296.0	74.0
0°-60°	1599.8	91.4
0°-90°	1750.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1750.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1452	
5°	1407	131
15°	1215	343
25°	1054	478
35°	539	344
45°	218	170
55°	150	133
65°	91	90
75°	44	47
85°	12	13
90°	0	



TEST NUMBER: P584033
CATALOG NUMBER: HCC8S20D010MB-HM80520927-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1451.6
2.5°	1438.6
5°	1406.7
7.5°	1361.8
10°	1308.6
12.5°	1258.9
15°	1215.2
17.5°	1173.8
20°	1137.2
22.5°	1100.6
25°	1054.5
27.5°	988.2
30°	894.8
32.5°	748.2
35°	539.0
37.5°	367.6
40°	281.3
42.5°	242.3
45°	217.5
47.5°	196.2
50°	178.5
52.5°	163.1
55°	150.1
57.5°	134.7
60°	119.4
62.5°	104.0
65°	91.0
67.5°	78.0
70°	65.0
72.5°	54.4
75°	43.7
77.5°	34.3
80°	26.0
82.5°	18.9
85°	11.8
87.5°	5.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)