

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584036

Luminaire Tested: **HCC8W20D010MW-HM80520927-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P584036
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8W20D010MW-HM80520927-81NDW
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
 CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1582.7 lumens
 Efficiency: N/A
 Efficacy: 79.1 lumens/watt
 Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 20
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P584036
CATALOG NUMBER: HCC8W20D010MW-HM80520927-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584036
 CATALOG NUMBER: HCC8W20D010MW-HM80520927-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39449
5°	39343
10°	38686
15°	38124
20°	37209
25°	35324
30°	29133
35°	15001
40°	10043
45°	8613
50°	7426
55°	6484
60°	5760
65°	5173
70°	4688
75°	4230
80°	3782
85°	3750



TEST NUMBER: P584036
 CATALOG NUMBER: HCC8W20D010MW-HM80520927-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.2	7.6
10°-20°	336.0	21.2
20°-30°	465.5	29.4
30°-40°	279.6	17.7
40°-50°	153.1	9.7
50°-60°	108.7	6.9
60°-70°	70.6	4.5
70°-80°	37.7	2.4
80°-90°	11.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	921.7	58.2
0°-40°	1201.3	75.9
0°-60°	1463.1	92.4
0°-90°	1582.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1582.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1279	
5°	1271	120
15°	1194	336
25°	1038	466
35°	398	280
45°	198	153
55°	121	109
65°	71	71
75°	36	38
85°	11	11
90°	0	



TEST NUMBER: P584036
CATALOG NUMBER: HCC8W20D010MW-HM80520927-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1279.3
2.5°	1276.9
5°	1271.0
7.5°	1256.8
10°	1235.5
12.5°	1215.5
15°	1194.2
17.5°	1167.0
20°	1133.9
22.5°	1093.7
25°	1038.2
27.5°	950.7
30°	818.2
32.5°	599.5
35°	398.5
37.5°	294.4
40°	249.5
42.5°	221.2
45°	197.5
47.5°	174.9
50°	154.8
52.5°	135.9
55°	120.6
57.5°	106.4
60°	93.4
62.5°	81.6
65°	70.9
67.5°	60.3
70°	52.0
72.5°	42.6
75°	35.5
77.5°	28.4
80°	21.3
82.5°	15.4
85°	10.6
87.5°	4.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)