

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584060

Luminaire Tested: **HCC8W20D010MB-HM80520930-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010MB-HM80520930-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2010.7 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584060
CATALOG NUMBER: HCC8W20D010MB-HM80520930-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584060

CATALOG NUMBER: HCC8W20D010MB-HM80520930-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40198
5°	40147
10°	39754
15°	39276
20°	38912
25°	38474
30°	36305
35°	29562
40°	16335
45°	10902
50°	9667
55°	9075
60°	8961
65°	8880
70°	8024
75°	7172
80°	6269
85°	5555



TEST NUMBER: P584060
 CATALOG NUMBER: HCC8W20D010MB-HM80520930-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	6.1
10°-20°	347.4	17.3
20°-30°	516.2	25.7
30°-40°	464.9	23.1
40°-50°	206.1	10.2
50°-60°	152.6	7.6
60°-70°	118.7	5.9
70°-80°	64.4	3.2
80°-90°	17.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	986.5	49.1
0°-40°	1451.4	72.2
0°-60°	1810.1	90.0
0°-90°	2010.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2010.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1304	
5°	1297	123
15°	1230	347
25°	1131	516
35°	785	465
45°	250	206
55°	169	153
65°	122	119
75°	60	64
85°	16	18
90°	0	



TEST NUMBER: P584060
CATALOG NUMBER: HCC8W20D010MB-HM80520930-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1303.6
2.5°	1301.0
5°	1297.0
7.5°	1286.6
10°	1269.6
12.5°	1250.0
15°	1230.3
17.5°	1210.6
20°	1185.8
22.5°	1161.0
25°	1130.8
27.5°	1085.0
30°	1019.6
32.5°	925.4
35°	785.3
37.5°	586.4
40°	405.8
42.5°	299.8
45°	250.0
47.5°	221.2
50°	201.5
52.5°	183.2
55°	168.8
57.5°	157.1
60°	145.3
62.5°	134.9
65°	121.7
67.5°	106.0
70°	89.0
72.5°	74.6
75°	60.2
77.5°	47.2
80°	35.3
82.5°	24.8
85°	15.7
87.5°	6.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)