

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584073

Luminaire Tested: **HCC8W20D010BZ-HM80520935-81RWWH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584073  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W20D010BZ-HM80520935-81RWWH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1913.2 lumens  
Efficiency: N/A  
Efficacy: 95.7 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584073  
CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584073

CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	31468	31468	31468
5°	32062	31335	30604
10°	32561	30789	29490
15°	32888	30021	28211
20°	32763	28861	26912
25°	31901	27195	25409
30°	30383	25210	23931
35°	27435	23008	22229
40°	24104	20654	20598
45°	20806	18154	18939
50°	18110	15922	16982
55°	16059	13827	14795
60°	14333	11687	12285
65°	12922	9485	9682
70°	11468	7105	5734
75°	9889	4110	2466
80°	7618	1474	728
85°	4883	495	495



TEST NUMBER: P584073  
 CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.8	5.0
10°-20°	266.7	13.9
20°-30°	377.2	19.7
30°-40°	397.5	20.8
40°-50°	337.8	17.7
50°-60°	243.3	12.7
60°-70°	140.3	7.3
70°-80°	48.0	2.5
80°-90°	6.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	739.7	38.7
0°-40°	1137.2	59.4
0°-60°	1718.3	89.8
0°-90°	1913.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1913.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1020	1020	1020	1020	1020	
5°	1036	1029	1012	994	989	99
15°	1030	998	940	899	884	290
25°	938	889	799	758	747	430
35°	729	686	611	589	590	454
45°	477	455	416	419	434	371
55°	299	275	257	267	275	269
65°	177	152	130	127	133	176
75°	83	62	34	22	21	88
85°	14	8	1	1	1	19
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584073

CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5
2.5°	1030.2	1031.6	1030.2	1030.2	1028.9	1027.5	1026.1	1024.8	1022.0	1019.2	1019.2
5°	1035.8	1038.5	1035.8	1035.8	1031.6	1028.9	1026.1	1022.0	1016.4	1012.3	1012.3
7.5°	1039.9	1039.9	1039.9	1035.8	1033.1	1028.9	1022.0	1015.1	1008.1	1001.3	998.4
10°	1039.9	1039.9	1038.5	1033.1	1030.2	1022.0	1015.1	1005.4	995.7	986.0	983.3
12.5°	1035.8	1037.2	1034.4	1028.9	1022.0	1012.3	1002.6	990.2	979.1	968.1	962.5
15°	1030.2	1028.9	1026.1	1019.2	1011.0	998.4	988.7	974.9	959.8	946.0	940.4
17.5°	1016.4	1016.4	1012.3	1005.4	994.3	980.5	965.2	950.1	933.4	918.3	911.3
20°	998.4	998.4	992.9	984.6	973.6	955.6	939.0	921.0	901.6	886.5	879.5
22.5°	972.2	973.6	966.6	956.9	944.5	923.7	907.2	885.1	865.7	847.7	842.2
25°	937.6	940.4	933.4	923.7	907.2	889.2	868.4	847.7	825.6	807.7	799.3
27.5°	897.5	898.9	891.9	882.2	865.7	846.3	825.6	803.5	782.7	763.3	755.1
30°	853.3	847.7	845.0	832.5	814.5	798.0	774.4	756.5	734.4	717.7	708.0
32.5°	791.0	793.8	785.4	775.9	762.0	742.7	723.3	702.5	681.8	669.4	662.4
35°	728.8	731.5	727.4	717.7	702.5	685.9	666.5	651.4	633.3	618.2	611.2
37.5°	663.8	663.8	661.0	655.5	644.4	629.2	609.9	594.7	579.4	567.0	562.9
40°	598.8	596.1	594.7	590.5	580.8	567.0	554.6	542.1	526.9	518.5	513.1
42.5°	535.2	535.2	532.4	528.2	518.5	511.7	499.3	485.4	474.3	466.1	466.1
45°	477.1	478.5	474.3	471.6	466.1	455.0	444.0	434.3	424.6	419.0	416.3
47.5°	426.0	426.0	421.7	419.0	413.5	403.8	394.1	385.8	378.9	374.8	373.4
50°	377.5	377.5	377.5	370.7	363.7	356.8	349.9	340.2	336.0	333.3	331.9
52.5°	336.0	334.6	334.6	329.2	322.2	313.9	307.0	298.7	294.6	291.8	293.1
55°	298.7	298.7	297.3	290.4	283.4	275.2	268.3	261.3	258.6	255.8	257.2
56°	283.4	283.4	282.1	276.6	268.3	261.3	253.1	246.2	242.0	243.4	243.4
57°	272.5	269.6	269.6	262.8	255.8	246.2	239.2	232.4	229.5	228.1	228.1
58°	258.6	257.2	255.8	248.9	242.0	233.7	226.8	219.9	215.7	215.7	214.3
59°	244.8	244.8	242.0	236.5	229.5	221.3	214.3	207.4	203.3	201.9	201.9
60°	232.4	233.7	229.5	224.0	218.6	208.9	200.5	195.0	190.9	189.5	189.5
61°	221.3	221.3	218.6	211.6	204.7	197.7	189.5	182.5	179.8	177.1	177.1
62°	211.6	208.9	207.4	200.5	193.6	185.3	178.4	171.5	167.4	164.5	166.0
63°	199.2	197.7	195.0	189.5	182.5	174.2	166.0	160.4	156.3	152.1	153.5
64°	189.5	188.1	183.9	178.4	171.5	163.2	154.8	149.4	146.6	142.4	141.0
65°	177.1	175.6	174.2	167.4	160.4	152.1	145.1	139.7	135.6	132.7	130.0
66°	166.0	167.4	164.5	159.0	150.7	143.8	134.2	128.6	125.9	121.7	118.9
67°	156.3	156.3	153.5	148.0	139.7	132.7	125.9	118.9	114.8	110.6	109.2
67.5°	150.7	150.7	148.0	141.0	135.6	127.2	120.3	114.8	109.2	106.5	103.7
68°	145.1	145.1	143.8	138.3	131.3	123.0	116.2	109.2	103.7	99.5	98.2
69°	135.6	136.9	134.2	128.6	121.7	113.4	106.5	100.9	95.4	91.3	88.5
70°	127.2	125.9	123.0	117.5	110.6	105.1	98.2	91.3	85.7	80.3	78.8
71°	116.2	116.2	113.4	109.2	102.4	95.4	88.5	83.0	77.4	70.6	69.1
72°	107.9	107.9	105.1	99.5	94.1	87.1	80.3	73.3	69.1	62.2	59.5
72.5°	102.4	103.7	100.9	95.4	89.8	81.6	76.0	70.6	63.6	58.0	55.3
73°	99.5	98.2	96.8	91.3	84.4	78.8	71.9	66.4	59.5	53.9	51.2



TEST NUMBER: P584073  
 CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	62.2	62.2	60.9	55.3	49.8	44.2	38.8	33.2	27.7	22.1	19.4
80°	42.9	44.2	41.5	38.8	34.5	29.1	23.5	19.4	13.8	11.1	8.3
82.5°	27.7	27.7	26.2	23.5	20.7	16.5	13.8	9.7	6.9	5.6	4.1
85°	13.8	15.2	13.8	12.4	9.7	8.3	6.9	4.1	2.7	1.4	1.4
87.5°	5.6	5.6	5.6	4.1	4.1	2.7	1.4	1.4	1.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584073

CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5	1020.5
2.5°	1016.4	1016.4	1013.7	1012.3	1011.0	1009.5	1008.1	1006.7	1006.7	1008.1
5°	1008.1	1005.4	999.9	998.4	994.3	992.9	990.2	988.7	990.2	988.7
7.5°	995.7	990.2	983.3	980.5	974.9	972.2	968.1	968.1	965.2	966.6
10°	979.1	970.8	962.5	956.9	952.8	948.7	946.0	943.1	941.8	941.8
12.5°	958.4	948.7	940.4	932.1	925.2	922.4	916.9	916.9	914.2	912.7
15°	934.8	922.4	912.7	904.5	898.9	893.4	889.2	886.5	883.7	883.7
17.5°	904.5	893.4	883.7	874.0	865.7	861.6	857.4	853.3	853.3	850.4
20°	871.3	858.8	850.4	840.8	833.9	826.9	821.5	821.5	818.7	820.1
22.5°	833.9	818.7	810.4	803.5	796.5	791.0	785.4	785.4	784.1	782.7
25°	792.4	780.0	770.3	762.0	757.8	752.3	750.9	748.2	746.8	746.8
27.5°	748.2	738.5	726.0	721.8	716.3	713.6	713.6	712.2	709.4	710.9
30°	701.2	690.1	683.2	680.4	674.8	674.8	673.5	670.7	670.7	672.1
32.5°	655.5	644.4	638.9	637.6	632.0	632.0	630.6	632.0	632.0	633.3
35°	605.7	596.1	594.7	590.5	589.1	589.1	589.1	591.8	594.7	590.5
37.5°	558.7	551.8	547.6	546.2	547.6	547.6	549.0	553.2	551.8	550.3
40°	510.3	504.7	502.0	502.0	504.7	507.6	507.6	511.7	513.1	511.7
42.5°	461.9	457.8	457.8	459.1	461.9	463.2	467.5	471.6	472.9	474.3
45°	416.3	416.3	416.3	417.6	419.0	421.7	427.3	431.4	432.8	434.3
47.5°	372.0	370.7	374.8	376.1	380.2	381.7	385.8	391.4	392.8	394.1
50°	330.5	333.3	334.6	338.8	341.6	341.6	347.2	349.9	354.0	354.0
52.5°	291.8	296.0	297.3	301.5	302.8	304.2	307.0	311.1	313.9	313.9
55°	257.2	258.6	261.3	262.8	266.9	268.3	271.0	272.5	276.6	275.2
56°	242.0	244.8	246.2	248.9	251.6	253.1	255.8	257.2	260.0	261.3
57°	228.1	229.5	233.7	235.1	237.8	237.8	239.2	243.4	243.4	244.8
58°	214.3	217.1	218.6	219.9	222.7	224.0	226.8	228.1	229.5	228.1
59°	201.9	203.3	204.7	204.7	207.4	207.4	211.6	214.3	215.7	215.7
60°	189.5	189.5	190.9	192.2	195.0	196.3	196.3	199.2	199.2	199.2
61°	177.1	177.1	178.4	179.8	181.2	181.2	183.9	183.9	185.3	186.6
62°	166.0	164.5	164.5	166.0	166.0	168.7	170.1	171.5	172.8	171.5
63°	153.5	152.1	152.1	152.1	152.1	154.8	154.8	156.3	159.0	157.7
64°	139.7	139.7	139.7	139.7	141.0	141.0	143.8	145.1	146.6	148.0
65°	130.0	127.2	125.9	125.9	127.2	128.6	130.0	131.3	132.7	132.7
66°	118.9	116.2	114.8	114.8	114.8	114.8	117.5	117.5	120.3	120.3
67°	106.5	103.7	102.4	100.9	100.9	100.9	105.1	103.7	103.7	103.7
67.5°	102.4	98.2	96.8	95.4	94.1	96.8	95.4	96.8	96.8	95.4
68°	96.8	94.1	91.3	88.5	88.5	88.5	89.8	91.3	89.8	88.5
69°	85.7	84.4	80.3	77.4	76.0	77.4	76.0	77.4	76.0	77.4
70°	76.0	71.9	67.7	66.4	65.0	65.0	65.0	63.6	65.0	63.6
71°	66.4	62.2	58.0	55.3	53.9	53.9	52.6	53.9	52.6	53.9
72°	56.7	52.6	47.0	44.2	44.2	44.2	44.2	42.9	44.2	42.9
72.5°	52.6	47.0	42.9	40.1	38.8	38.8	38.8	38.8	37.4	38.8
73°	48.3	42.9	37.4	35.9	35.9	35.9	34.5	33.2	34.5	34.5





TEST NUMBER: P584073  
 CATALOG NUMBER: HCC8W20D010BZ-HM80520935-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	16.5	12.4	11.1	11.1	11.1	11.1	11.1	11.1	9.7	9.7
80°	6.9	5.6	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
82.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
85°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	89.8	89.8	87.1	83.0	76.0	69.1	63.6	58.0	51.2	44.2	41.5
75°	83.0	81.6	78.8	74.7	69.1	62.2	56.7	49.8	44.2	37.4	34.5

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	40.1	33.2	30.4	27.7	27.7	27.7	26.2	26.2	26.2	27.7
75°	31.8	26.2	23.5	20.7	22.1	20.7	22.1	20.7	20.7	20.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)