

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593611

Luminaire Tested: **HCC8W20D010BZ-HM80520950-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010BZ-HM80520950-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2116.7 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593611
CATALOG NUMBER: HCC8W20D010BZ-HM80520950-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593611
 CATALOG NUMBER: HCC8W20D010BZ-HM80520950-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49		
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49687
5°	49037
10°	47240
15°	45393
20°	44140
25°	42809
30°	38416
35°	25184
40°	13924
45°	11609
50°	10588
55°	10102
60°	9387
65°	8515
70°	7709
75°	6958
80°	6322
85°	6050



TEST NUMBER: P593611
 CATALOG NUMBER: HCC8W20D010BZ-HM80520950-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.8	7.0
10°-20°	401.2	19.0
20°-30°	570.9	27.0
30°-40°	422.5	20.0
40°-50°	209.3	9.9
50°-60°	167.0	7.9
60°-70°	115.9	5.5
70°-80°	62.5	3.0
80°-90°	18.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1120.9	53.0
0°-40°	1543.5	72.9
0°-60°	1919.8	90.7
0°-90°	2116.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2116.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1611	
5°	1584	149
15°	1422	401
25°	1258	571
35°	669	423
45°	266	209
55°	188	167
65°	117	116
75°	58	63
85°	17	18
90°	0	



TEST NUMBER: P593611
CATALOG NUMBER: HCC8W20D010BZ-HM80520950-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1611.3
2.5°	1604.1
5°	1584.2
7.5°	1552.9
10°	1508.7
12.5°	1463.2
15°	1421.9
17.5°	1382.1
20°	1345.1
22.5°	1308.1
25°	1258.2
27.5°	1185.7
30°	1078.9
32.5°	915.2
35°	669.0
37.5°	456.8
40°	345.9
42.5°	296.1
45°	266.2
47.5°	242.0
50°	220.7
52.5°	202.1
55°	187.9
57.5°	170.8
60°	152.2
62.5°	133.8
65°	116.7
67.5°	99.6
70°	85.5
72.5°	71.2
75°	58.4
77.5°	46.9
80°	35.6
82.5°	25.6
85°	17.1
87.5°	7.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)